

Slim Micro USB 3.0 (5Gbps) Cable - M/M - 2m (6ft)

Product ID: USB3AUB2MS



Does your regular USB 3.2 Gen 1 cable lift or push against your external hard drive causing it to move around on your desk? Are you forced to arrange your desk according to how your cable decides to bend and rest?

The USB3AUB2MS features a slim USB wire construction that makes it easier to install your USB 3.2 Gen 1 devices and enables you to place them as needed throughout your workspace. Plus, the thin Micro USB connector molding makes this a great cable for mobile USB 3.2 Gen 1 devices too - it lets you plug into your device without having to take it out of its case for every charge and sync.

Organize your desk and your office to match your needs. This durable, lightweight cable is approximately half the thickness of a regular USB 3.2 Gen 1 cable giving you the freedom to place your devices as needed and with minimal clutter. The flexible, thin cable also reduces strain on the connection and prevents damage to the USB 3.2 Gen 1 port on your device.

Provide full charging power, with no loss of charge time, even at distances of up to 6 feet (2 meters) away from your charger.

As well as being ideal for connecting to your desktop devices, this cable provides the perfect solution for charging and syncing your USB 3.2 Gen 1 Micro B-equipped phones and tablets.

The long charge cable overcomes distance restrictions and lets you stay connected even while you're taking notes in a boardroom, catching up on emails in a hotel room, or reading in a coffee shop.

Stop removing the case from your phone or tablet every time you charge or sync your device. The cable offers a thin Micro USB connector molding that plugs into your device even while it's inside a protective case.

This Micro USB 3.2 Gen 1 cable is backed by StarTech.com's Lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility



Applications

- Connect Micro USB 3.0 devices (portable hard drive, card reader, video capture device, hard drive enclosure, etc.) to a USB 3.0 compatible PC or laptop
- Charge and sync your USB 3.0 Micro B-equipped mobile digital devices

Features

- Slim cable construction – outer diameter (OD) of 4.8mm
- Redesigned, thin Micro USB 3.2 Gen1 connector molding
- Supports USB 3.2 Gen1 data transfer rates up to 5Gbps
- Cable and connectors are compliant with USB 3.2 Gen1 SuperSpeed specifications
- Aluminum-Mylar Foil with Braided Shielding
- Molded connectors with strain relief

Hardware

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

Connector(s)

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB 3.0 Micro-B (10 pin, SuperSpeed)

Physical Characteristics

Color	Black
-------	-------

Connector Style	Straight
Wire Gauge	26/32 AWG
Cable Length	6.6 ft [2 m]
Product Length	6.6 ft [2.0 m]
Product Width	0.0 in [0.0 cm]
Product Height	0.0 in [0.0 cm]
Weight of Product	2.1 oz [59.0 g]

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.7 cm]
Package Width	7.6 in [19.4 cm]
Package Height	0.8 in [2.1 cm]
Shipping (Package) Weight	3.3 oz [94.0 g]

What's in the Box

Included in Package	1 - 2m (6ft) Slim SuperSpeed USB 3.0 A to Micro B Cable - M/M
---------------------	---

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*

