

10 ft Black SuperSpeed USB 3.0 (5Gbps) Cable A to B - M/M

**Product ID:** USB3SAB10BK



StarTech.com's 10ft Black SuperSpeed USB 3.2 Gen 1 cable (A-B, male-male) offers a durable, high quality connection that harnesses the full capability of the USB 3.2 Gen 1 standard.

Designed for next-generation SuperSpeed USB device connections, the 10ft USB 3.2 Gen 1 cable offers a throughput of up to 5Gbps when used with a USB 3.2 Gen 1 host and device - an astounding 10x the capability of USB 2.0 (480Mbps).

Our 10ft USB 3.2 Gen 1 cable features high quality Shielded Twisted Pair (STP) construction, helping to prevent electro-magnetic interference and ensuring reliable data communication.

The 10ft USB 3.2 Gen 1 cable is backed by our Lifetime Warranty, providing guaranteed quality and reliability.

## Certifications, Reports and Compatibility



## Applications

- Connect a SuperSpeed USB 3.0 device to an USB 3.0 capable PC, Notebook, or Server

## Features

- Molded connectors with strain relief
- Designed and constructed to SuperSpeed USB 3.2 Gen1 Specifications

---

**Hardware**

|                       |                            |
|-----------------------|----------------------------|
| Warranty              | Lifetime                   |
| Cable Jacket Material | PVC - Polyvinyl Chloride   |
| Cable Shield Material | Foil shielded twisted pair |

---

**Performance**

|               |                    |
|---------------|--------------------|
| Type and Rate | USB 3.0 - 5 Gbit/s |
|---------------|--------------------|

---

**Connector(s)**

|             |  |
|-------------|--|
| Connector A | 1 - USB Type-A (9 pin, 5 Gbps)           |
| Connector B | 1 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps) |

---

**Environmental**

|                       |                           |
|-----------------------|---------------------------|
| Operating Temperature | -10C to 50C (14F to 122F) |
| Storage Temperature   | -20C to 60C (-4F to 140F) |
| Humidity              | 0~75% RH                  |

---

**Physical Characteristics**

|                   |                  |
|-------------------|------------------|
| Color             | Black            |
| Wire Gauge        | 28 AWG           |
| Cable Length      | 10.0 ft [3.0 m]  |
| Product Length    | 10.0 ft [3.0 m]  |
| Product Width     | 0.5 in [1.4 cm]  |
| Product Height    | 0.5 in [1.2 cm]  |
| Weight of Product | 4.6 oz [129.7 g] |

---

**Packaging Information**

|                  |                  |
|------------------|------------------|
| Package Quantity | 1                |
| Package Length   | 7.1 in [18.1 cm] |
| Package Width    | 5.9 in [15.0 cm] |

Package Height 1.1 in [2.8 cm]

Shipping (Package) Weight 4.9 oz [138.0 g]

---

**What's in the Box**

Included in Package 1 - 10ft black USB 3.0 A to B cable

---

**Warranty  
Information**

Warranty Lifetime

---

*\*Product appearance and specifications are subject to change without notice.*

