

USB OTG Cable - Micro USB to Micro USB - M/M - 8 in.

**Product ID:** UUUSBOTG8IN



Now, you can download confidential information from your smartphone or tablet to an external drive, without having to use a Wi-Fi or mobile data connection. This 8 in. USB OTG cable gives you the perfect solution for backing up your important research and other data collected while you're on the road.

The cable turns the Micro-USB port on your mobile device into a USB OTG host port, so that you can connect a Micro-USB drive or other Micro-USB device, such as a game controller, directly to your phone or tablet.

The OTG cable features a compact design that's perfect for carrying as a tablet accessory.

The UUUSBOTG8IN is backed by StarTech.com's lifetime warranty for guaranteed reliability.

**Please Note:** This adapter will only work with devices that support USB OTG. Please consult your documentation and/or your service provider to ensure that your device supports USB OTG functionality.

## Certifications, Reports and Compatibility



## Applications

- Connect a Micro-USB external drive or other Micro-USB device, such as a game controller, directly to your Micro-USB mobile device
- Download confidential information from your mobile device directly to your external drive
- Back up research and field data to your external drive

## Features

- Support for USB OTG (On-the-Go) capable devices
- Portable design that's perfect for use as a tablet accessory
- Guaranteed reliability with a lifetime warranty

---

### Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | Lifetime                       |
| Connector Plating     | Nickel                         |
| Cable Jacket Material | PVC - Polyvinyl Chloride       |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

---

### Connector(s)

|             |                         |
|-------------|-------------------------|
| Connector A | 1 - USB Micro-B (5 pin) |
| Connector B | 1 - USB Micro-B (5 pin) |

---

### Physical Characteristics

|                   |                   |
|-------------------|-------------------|
| Color             | Black             |
| Connector Style   | Straight          |
| Wire Gauge        | 28 AWG            |
| Cable Length      | 8.0 in [203.2 mm] |
| Product Length    | 8.0 in [20.3 cm]  |
| Product Width     | 0.4 in [0.9 cm]   |
| Product Height    | 0.2 in [0.6 cm]   |
| Weight of Product | 0.4 oz [11.2 g]   |

---

### Packaging Information

|                  |                  |
|------------------|------------------|
| Package Quantity | 1                |
| Package Length   | 4.3 in [11.0 cm] |

Package Width 5.0 in [12.7 cm]

Package Height 0.5 in [1.2 cm]

Shipping (Package)  
Weight 0.7 oz [20.0 g]

---

#### What's in the Box

|                     |  |
|---------------------|--|
| Included in Package | 1 - 8in Micro-USB to Micro-USB OTG Cable - M/M |
|---------------------|--|

---

#### Warranty Information

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

***\*Product appearance and specifications are subject to change without notice.***

