

**VT CTL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

**General ordering data**

|            |                               |
|------------|-------------------------------|
| Version    | Testing tools, Testing device |
| Order No.  | <a href="#">2436690000</a>    |
| Type       | VT CTL                        |
| GTIN (EAN) | 4050118450040                 |
| Qty.       | 1 pc(s).                      |

## VT CTL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |
|------------|---------|
| Net weight | 143.5 g |
|------------|---------|

## Technical data

|                        |                    |
|------------------------|--------------------|
| Description of article | Continuity testers |
|------------------------|--------------------|

## Measuring and testing devices

|                            |                        |                                  |                        |
|----------------------------|------------------------|----------------------------------|------------------------|
| AC voltage measuring range | 0.1 - 400 V            | Battery type                     | 1.5 V type AAA battery |
| Continuity test            | Yes - optical + buzzer | Display                          | Visual & acoustic      |
| Protection degree          | IP44                   | Tested and approved according to | DIN EN 61010-1         |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000494    | ETIM 7.0    | EC000494    |
| ETIM 8.0    | EC000494    | ETIM 9.0    | EC000494    |
| ETIM 10.0   | EC000494    | ECLASS 9.0  | 27-20-03-08 |
| ECLASS 9.1  | 27-20-03-08 | ECLASS 10.0 | 27-20-03-08 |
| ECLASS 11.0 | 27-20-03-08 | ECLASS 12.0 | 27-20-03-08 |
| ECLASS 13.0 | 27-20-03-08 | ECLASS 14.0 | 27-20-03-08 |
| ECLASS 15.0 | 27-20-03-08 |             |             |

## Environmental Product Compliance

|                        |                                      |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant                            |
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | b05b5122-6117-4cb0-b28c-df32f921fa36 |

## Approvals

Approvals



|                 |                                                                                                                                                                             |
|-----------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Approvals MAMID | <a href="https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/">https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/</a> |
| ROHS            | Conform                                                                                                                                                                     |

## Downloads

|                    |                                          |
|--------------------|------------------------------------------|
| User Documentation | <a href="#">Manual</a>                   |
| Catalogues         | <a href="#">Catalogues in PDF-format</a> |

## VT CTL

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Drawings

