

IE-FC-SET-IPDED003-KY-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

FrontCom® Vario integrates multiple functions in only one single frame. The system is easy to install and you can select from a wide range of data, signal and power modules. In addition to being extremely compact, FrontCom® Vario offers a number of unique product features that will make your project planning and work activities secure, fast and future-proof. Furthermore, the FrontCom® Vario system has an attractive housing design that, by the way, offers highest impact-resistance and fully meets the requirements of IP 65 protection class.

General ordering data

Version	FrontCom, Set
Order No.	2460640000
Type	IE-FC-SET-IPDED003-KY-M
GTIN (EAN)	4050118478150
Qty.	1 pc(s).
Reference product	1450520000 1450630000 1450730000 1019570000

IE-FC-SET-IPDED003-KY-M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	134 mm	Depth (inches)	5.276 inch
Height	40 mm	Height (inches)	1.575 inch
Width	67 mm	Width (inches)	2.638 inch
Net weight	634 g		

General data

Material cover	Zinc diecast, powder-coated	Material frame	Zinc diecast
Product type	Set	Protection degree	IP65, in closed state

Technical data

Data inserts	USB 2.0 A/A	Frame	Metal cover, Lockable with key
Insert plate	1x data, 1x power, Unshielded	Power inserts	Socket DE
Rated current for socket	16 A	Rated voltage for socket	250 V

Classifications

ETIM 6.0	EC001031	ETIM 7.0	EC001031
ETIM 8.0	EC001031	ETIM 9.0	EC001031
ETIM 10.0	EC001031	ECLASS 9.0	27-18-27-02
ECLASS 9.1	27-18-27-90	ECLASS 10.0	27-18-27-02
ECLASS 11.0	27-18-27-02	ECLASS 12.0	27-18-28-92
ECLASS 13.0	27-18-28-92	ECLASS 14.0	27-18-28-92
ECLASS 15.0	27-18-28-92		

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	8a473a8a-33d4-4318-8088-c28f019e7f77

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN

IE-FC-SET-IPDED003-KY-M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

