

POWERCRIMPER 6.0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

The rationalisation of crimping processes calls for more and more automation of the individual steps. "Optimisation of installation times" is what the markets of the future will be demanding of their strategic partners. Automatic machines that permit rational processing of conductor materials represent the answer to an approach geared to future needs. Versatility and functionality are decisive factors for the customer. With our comprehensive line of automated machinery, Weidmüller provides professional and efficient solutions for cable preparation and processing.

General ordering data

Version	Crimping machine, 0.5mm ² , 6mm ²
Order No.	2634310000
Type	POWERCRIMPER 6.0
GTIN (EAN)	4050118660906
Qty.	1 pc(s).

POWERCRIMPER 6.0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	405 mm	Depth (inches)	15.945 inch
Height	240 mm	Height (inches)	9.449 inch
Width	165 mm	Width (inches)	6.496 inch
Net weight	15,848 g		

Automatic crimping

Compressed-air connection		Consumables	With and without plastic collar, Twin wire-end ferrules
	5 - 5.5 bar		
Crimping length	6 - 18 mm	Crimping range	0.5...6 mm ²
Crimping range, max.	6 mm ²	Crimping range, min.	0.5 mm ²
Drive		Electrical connection	100 - 240 V / 50/60 Hz / 16 VA
	Electropneumatic		
Insertion length		Note	Twin wire-end ferrules in the cross-section range from 2 x 0.5 to 2 x 2.5 mm ² , No need to change tools
	13		
Pulse time	approx. 1 s	Wire end ferrules cross-section, max.	6 mm ²
Wire end ferrules cross-section, min.	0.5 mm ²		

Classifications

ETIM 6.0	EC002778	ETIM 7.0	EC002778
ETIM 8.0	EC002778	ETIM 9.0	EC002778
ETIM 10.0	EC002778	ECLASS 9.1	17-31-01-01
ECLASS 10.0	17-13-01-01	ECLASS 11.0	17-13-01-01
ECLASS 12.0	17-13-01-01	ECLASS 13.0	17-13-01-01
ECLASS 14.0	17-13-01-01	ECLASS 15.0	17-13-01-01

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c, 7a, 7cl
REACH SVHC	Lead 7439-92-1
SCIP	d2df479e-2b79-4e98-adc7-b03577df98ae

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319222/-T1z1mm-S800/
ROHS	Conform

Downloads

User Documentation	Manual
Catalogues	Catalogues in PDF-format

POWERCRIMPER 6.0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

