

STB05-BLANK-1

✓ ACTIVE

Agastat 7000


TE Internal #: 2-1768038-6

Brown Pre-Printed Marker, Snap-On, Size 5, White Print, Straight Cut, 3.2 mm [.126 in] Width, Thermoplastic, Agastat 7000

[View on TE.com >](#)



Identification & Labeling > Pre-Printed Markers > STD Snap-On Markers



Marker Style: **Snap-On**

Marker Size: **5**

Compatible Cable Diameter Range: **2.3 – 3 mm [.091 – .118 in]**

Primary Product Color: **Brown**

Marker Cut: **Straight**

[All STD Snap-On Markers \(957\)](#)

Features

Body Features

Marker Style	Snap-On
Marker Size	5
Primary Product Color	Brown
Primary Product Material	Thermoplastic

Dimensions

Compatible Cable Diameter Range	2.3 – 3 mm[.091 – .118 in]
Product Width	3.2 mm[.126 in]

Printer/Label Features

Marker Cut	Straight
------------	----------

Other

Printed Marking Color	White
-----------------------	-------

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




Also in the Series | Agastat 7000

STB05-BLANK-1

Brown Pre-Printed Marker, Snap-On, Size 5, White Print, Straight Cut, 3.2 mm [.126 in] Width, Thermoplastic, Agastat 7000



DC Relays(32)



Pre-Printed Markers(957)



Time Delay Relays(39)

Documents

Product Drawings

STB05-BLANK-1

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1768038-6_O.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1768038-6_O.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1768038-6_O.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

STD and STB Technical Datasheet

English

Cable Identification Product Shelf Life

English