

HDC MBUS 2 F MCLIP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Flexible**

The four module sizes make for individual plug solutions that save a huge amount of space. The smaller pitch translates into an optimised design too.

General ordering data

Version	Data module, Number of poles: , Crimp connection, Female, Required plug-in slots: 1
Order No.	2667180000
Type	HDC MBUS 2 F MCLIP
GTIN (EAN)	4050118803860
Qty.	1 pc(s).

HDC MBUS 2 F MCLIP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	41.2 mm	Height (inches)	1.622 inch
Width	14.5 mm	Width (inches)	0.571 inch
Net weight	2.2 g		

Temperatures

Limit temperature	-40 °C ... 125 °C
-------------------	-------------------

General data

Insulation strength	$10^{12} \Omega$	Material	Polycarbonate, glass fibre reinforced
Plugging cycles	≥ 500	Pollution severity	3
Required plug-in slots	1	Series	ModuPlug
Surge voltage category	III	Type	Female
UL 94 flammability rating	V-0		

PE connection data

Connection type PE	Screw connection via module frame
--------------------	-----------------------------------

Version

Type of connection	Crimp connection
--------------------	------------------

Classifications

ETIM 6.0	EC002641	ETIM 7.0	EC002641
ETIM 8.0	EC002641	ETIM 9.0	EC002641
ETIM 10.0	EC002641	ECLASS 9.0	27-44-03-12
ECLASS 9.1	27-44-02-18	ECLASS 10.0	27-44-03-12
ECLASS 11.0	27-44-03-12	ECLASS 12.0	27-44-03-12
ECLASS 13.0	27-44-03-12	ECLASS 14.0	27-44-03-12
ECLASS 15.0	27-44-03-12		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1609748e-c278-4c9b-b3d1-e6215d2988cd

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

HDC MBUS 2 F MCLIP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

