



HW

TE Internal #: E07443-000

White, Industrial Label, Die-Cut, High Tack Permanent Acrylic Adhesive, 50.8 mm [2 in] Width, 25.4 mm [1 in] Height, Polyester, HW, Standard Labels

[View on TE.com >](#)

Identification & Labeling > Labels > Standard Labels > HW High Tack White Polyester Labels



Label Type: Industrial Label

Label Style: Die-Cut

Label Adhesive Type: High Tack Permanent Acrylic Adhesive

Compatible With Agency/Standards Products: UL

Product Width: 50.8 mm [2 in]

[All HW High Tack White Polyester Labels \(44\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	White
Primary Product Material	Polyester

Dimensions

Product Width	50.8 mm[2 in]
Product Height	25.4 mm[1 in]

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	1
Label Style	Die-Cut
Length of Label Roll	143 m[469.16 ft]
Label Thickness	97 Micron

Industry Standards

--	--

Compatible With Agency/Standards Products	UL
---	----

Packaging Features

Packaging Method	Roll
Packaging Quantity	5000

Other

Label Adhesive Type	High Tack Permanent Acrylic Adhesive
---------------------	--------------------------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2025 (250) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # 1-2186501-1
T3212-SWARE-PRINTER



TE Part # 1-2186502-1
T3224-PRINTER




TE Part # 1-2186503-1
T3224-SWARE-PRINTER



TE Part # 1-2186500-1
T3212-PRINTER

Also in the Series | HW




Standard Labels(44)

Customers Also Bought



TE Part #809133-000
202D242-3/42-0




TE Part #2-644489-5
05P MTA100 SHRD HDR R/A 30AU L




TE Part #4-794619-4
14P MICRO MNL ASSY,R/A,HDR LF



TE Part #6-1617753-7
FCA-325-CY9



TE Part #3-1744163-4
04P MTA100 HDR ASSY SM 30AU LF




TE Part #7-1879269-7
RP 2A 40R2 0.1% 15PPM 1K RL




TE Part #2-1879509-7
CRGH0805 1% 200R 0.33W



TE Part #4-2176380-6
RQ 0805 3K4 0.1% 10PPM 5K RL



TE Part #2841-5-14300
CONT PIN



TE Part #2187615-1
SW PIR RECT, 100OHM, 9X6SP, COL1 /6 BLANK



Documents

Product Drawings

[HW-508254-5-9](#)

English

Datasheets & Catalog Pages

[HW High Tack White Polyester labels](#)

English

[IDENTIFICATION SELECTION GUIDE](#)

English

Product Specifications

[IDENTIFCATION PRINTER PRODUCT RIBBON MATRIX](#)

English