

**ISPF QB58 BL****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image****General ordering data**

|            |                               |
|------------|-------------------------------|
| Version    | Insulation profile, PVC, blue |
| Order No.  | <a href="#">0546080000</a>    |
| Type       | ISPF QB58 BL                  |
| GTIN (EAN) | 4008190927035                 |
| Qty.       | 10 pc(s).                     |

## ISPF QB58 BL

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |        |                 |             |
|------------|--------|-----------------|-------------|
| Depth      | 5.7 mm | Depth (inches)  | 0.224 inch  |
| Height     | 465 mm | Height (inches) | 18.307 inch |
| Width      | 2.5 mm | Width (inches)  | 0.098 inch  |
| Net weight | 5.88 g |                 |             |

## Temperatures

|                     |               |
|---------------------|---------------|
| Ambient temperature | -5 °C...40 °C |
|---------------------|---------------|

## Material data

|                           |     |        |      |
|---------------------------|-----|--------|------|
| Material                  | PVC | Colour | blue |
| UL 94 flammability rating | V-0 |        |      |

## System specifications

|         |               |
|---------|---------------|
| Version | Cover profile |
|---------|---------------|

## Additional technical data

|                          |         |                     |                 |
|--------------------------|---------|---------------------|-----------------|
| Explosion-tested version | No      | Installation advice | Direct mounting |
| Type of fixing           | Plugged | Type of mounting    | Plugged         |

## General

|                     |                 |
|---------------------|-----------------|
| Installation advice | Direct mounting |
|---------------------|-----------------|

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002848    | ETIM 7.0    | EC002848    |
| ETIM 8.0    | EC002848    | ETIM 9.0    | EC002848    |
| ETIM 10.0   | EC002848    | ECLASS 9.0  | 27-14-11-92 |
| ECLASS 9.1  | 27-14-11-92 | ECLASS 10.0 | 27-14-11-92 |
| ECLASS 11.0 | 27-14-11-92 | ECLASS 12.0 | 27-14-11-92 |
| ECLASS 13.0 | 27-25-03-90 | ECLASS 14.0 | 27-25-03-90 |
| ECLASS 15.0 | 27-25-03-90 |             |             |

## Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

## Environmental Product Compliance

|                        |                             |
|------------------------|-----------------------------|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC             | No SVHC above 0.1 wt%       |

## Downloads

|                                             |                                                                                                     |
|---------------------------------------------|-----------------------------------------------------------------------------------------------------|
| Approval/Certificate/Document of Conformity | <a href="#">Confirmation of Standards EN 45545-2_2020-10</a>                                        |
| Engineering Data                            | <a href="#">CAD data – STEP</a><br><a href="#">CAD data – DWG</a><br><a href="#">CAD data – DXF</a> |
| User Documentation                          | <a href="#">StorageConditionsTerminalBlocks</a>                                                     |

Creation date July 15, 2025 10:03:21 PM CEST

Catalogue status 04.07.2025 / We reserve the right to make technical changes.