

**PAC-S7300-HE20-V18-10M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

The pre-assembled PAC cables establish an electrical and logical connection between the PLC and the PLC interfaces. These cables consist of the following components:

- Manufacturer's PLC connector.
- Multi-pole LIYY or LY YCY cable (shielded) with a cross-section of 0.14 mm<sup>2</sup> or 0.25 mm<sup>2</sup>.
- Flat cable connector, SUB-D or RSV, for connection to the interface.

The cables are tested automatically for their continuity and insulation to guarantee the functionality for which they have been designed.

**General ordering data**

|                 |                                                  |
|-----------------|--------------------------------------------------|
| Version         | Pre-assembled cable, PAC, Cable LiYY, 8.6 ± 1 mm |
| Order No.       | <a href="#">1431530100</a>                       |
| Type            | PAC-S7300-HE20-V18-10M                           |
| GTIN (EAN)      | 4032248175581                                    |
| Qty.            | 1 pc(s).                                         |
| Available until | 2014-05-20                                       |

**PAC-S7300-HE20-V18-10M****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Technical data****Dimensions and weights**

|            |         |
|------------|---------|
| Net weight | 2,114 g |
|------------|---------|

**Temperatures**

|                     |             |                       |             |
|---------------------|-------------|-----------------------|-------------|
| Storage temperature | -10...60 °C | Operating temperature | -10...50 °C |
|---------------------|-------------|-----------------------|-------------|

**General Data**

|                    |                                            |                       |                                       |
|--------------------|--------------------------------------------|-----------------------|---------------------------------------|
| Cable              | Cable LiYY                                 | Cable length          | 10 m                                  |
| Connector PLC side | SIEMENS S7300<br>6ES7921-3AH20-1AA0<br>40P | Interface connector   | 2X FLAT CABLE CONNec-<br>TOR HE10 20P |
| Material           | PVC                                        | Number of poles, min. | 20-pole                               |
| Outer diameter     | 8.6 ± 1 mm                                 | Suitable for          | Digital signals                       |
| Wire cross-section | 0.25 mm <sup>2</sup>                       |                       |                                       |

**Electrical Data**

|                     |                     |                                             |           |
|---------------------|---------------------|---------------------------------------------|-----------|
| High voltage test   | 1 kV/1s             | Permissible current strength per path, max. | 1 A       |
| Rated voltage       | ≤ 60 V DC ≤ 25 V AC | Resistance                                  | ≤ 80 mΩ/m |
| Total current, max. | 3 A                 |                                             |           |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000237    | ETIM 7.0    | EC000237    |
| ETIM 8.0    | EC000237    | ETIM 9.0    | EC000237    |
| ETIM 10.0   | EC000237    | ECLASS 9.0  | 27-24-22-20 |
| ECLASS 9.1  | 27-24-22-20 | ECLASS 10.0 | 27-24-22-20 |
| ECLASS 11.0 | 27-24-22-20 | ECLASS 12.0 | 27-24-22-20 |
| ECLASS 13.0 | 27-24-22-20 | ECLASS 14.0 | 27-24-22-20 |
| ECLASS 15.0 | 27-24-22-20 |             |             |

**Environmental Product Compliance**

|                        |                                      |
|------------------------|--------------------------------------|
| RoHS Compliance Status | Compliant                            |
| REACH SVHC             | Lead 7439-92-1                       |
| SCIP                   | 4bbf2c0d-0764-4fc8-bb24-9351c28c190d |

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|