

Backplane Selection Guide

Rackmount Chassis

PICMG 1.0	Slots per Segment			PCI-X	Compatible Chassis									
	PICMG	PCI	ISA		RK-110S	RK-190	RK210S	RK-220	RK-260	RK-410FS	RK-440	RK-460	RK-610	RK-615FB
HPCI-D3S2	1	2	-	-	✓									
HPCI-D6S4	1	4	1	-			✓	✓	✓					
HPCI-13S4LU	3	4	9	-						✓		✓	✓	✓
HPCI-14S7U	3	7	7	-						✓		✓	✓	✓
HPCI-14S12U	2	12	2	-						✓		✓	✓	✓
HPCI-14S/ATX	2	4	9	-						✓		✓	✓	✓
HPCI-15S	2	4	10	-									✓	✓
HPCI-15S10	2	10	4	-									✓	✓
HPCI-19S18A	2	18	1	-							✓			
PICMG 1.3	PICMG	PCI	PCI-E			PCI-X	RK-110SE	RK-210E	RK-220E					
			x1	x4	x16									
EBP-10E5	1	4	4		1	-					✓		✓	✓
EBP-13E2	1	10	-	1	1	-					✓		✓	✓
EBP-13E4	1	7	-	3	1	-					✓		✓	✓
EBP-16Q8	4	4	-	4	4	-						✓		
EBP-D5E2	1	2	-	1	1	-		✓	✓					
EBP-D3S1	1	1	-		-	-	✓							
EBP-D3E1	1	-	-	1	-	-	✓							
EBP-1UX4	1	-	-	2	-	-		✓						

Wallmount Chassis

PICMG 1.0	Slots per Segment			PCI-X	Compatible Chassis		
	PICMG	PCI	ISA		RK-606UC	RK-607B	RK-608B-E
HPCI-6S4	1	4	1	-	✓	✓	
HPCI-8S4	2	4	4	-			✓
HPCI-9S7U	2	7	2	-			✓
PICMG 1.3	PICMG	PCI	PCI-E			PCI-X	
			x1	x4	x16		
EBP-5E1	1	2	-	-	1	-	✓
EBP-7E2	1	4	-	1	1	-	✓
EBP-9E2	1	6	-	1	1	-	✓

Backplane Selection Guide

Single Board Computers

PICMG1.0	Slots per Segment			ISA	Compatible SBCs				
	PICMG	PCI	PCI-X		NuPRO-A331	NuPRO-935A	NuPRO-730	NuPRO-A301	NuPRO-852
HPCI-D3S2	1	2	-	-	✓	✓	✓	✓	✓
HPCI-D6S4	1	4	-	1	✓	✓	✓	✓	✓
HPCI-6S4	1	4	-	1	✓	✓	✓	✓	✓
HPCI-8S4	2	4	-	4	✓	✓	✓	✓	✓
HPCI-9S7U	2	7	-	2	✓	✓	✓	✓	✓
HPCI-13S4LU	3	4	-	9	✓	✓	✓	✓	✓
HPCI-14S7U	3	7	-	7	✓	✓	✓	✓	✓
HPCI-14S12U	2	12	-	2	✓	✓	✓	✓	✓
HPCI-14S/ATX	2	4	-	9	✓	✓	✓	✓	✓
HPCI-15S	2	4	-	10	✓	✓	✓	✓	✓
HPCI-15S10	2	10	-	4	✓	✓	✓	✓	✓
HPCI-19S18A	2	18	-	1	✓	✓	✓	✓	✓

PICMG1.3	Slots per Segment			PCI-E			Compatible SBCs				
	PICMG	PCI	PCI-X	x1	x4	x16	NuPRO-E340	NuPRO-E330	NuPRO-E315	NuPRO-E320	NuPRO-965
EBP-5E1	1	2	1	-	-	1	✓	✓	✓	✓	✓
EBP-7E2	1	4	-	-	1	1	✓	✓	✓	✓	✓
EBP-9E2	1	6	-	-	1	1	✓	✓	✓	✓	✓
EBP-10E5	1	4	-	4	-	1	✓	✓	✓	✓	✓
EBP-13E2	1	10	-	-	1	1	✓	✓	✓	✓	✓
EBP-13E4	1	7	-	-	3	1	✓	✓	✓	✓	✓
EBP-16Q8	1	1	-	-	1	1	-	-	✓	✓	✓
EBP-D5E2	1	2	-	-	1	1	✓	✓	✓	✓	✓
EBP-D3S1	1	1	-	-	-	-	✓	✓	✓	✓	✓
EBP-D3E1	1	-	-	-	1	-	✓	✓	✓	✓	✓
EBP-1UX4	1	-	-	-	2	-	✓	✓	✓	✓	✓