

Specification Sheet

Part Number: 151-04218

Multiple cradle pockets separate power and signal runs.

EZ-in / EZ-out retention pins retain wires during build out and allow future access to add or remove wires.

EZ Feed groove for obstruction-free insertion of a cable tie to cinch down bundle if needed.

CutZone creates guide for safely removing cable tie.



Quick-mount options using M6 (#10) screws in holes or slots for easy positioning and adjustability.

Cable Stacker Mount, 3-Pocket, Screw Mount, PA66HIRHSUV, Black, 10/pkg

Article Number 151-04218

Type CBLSTK3CZS

Color Black (BK)

Quantity Per bag

Product Description

HellermannTyton's Cable Stacker Mount is a cable management device used to organize and mount wires and relieve congestion along wire pathways found in conveyor systems and automation equipment. These mounts feature individual cradle partitions which enable faster installs and reduced rework and improve appearance and aesthetics. The EZ Build concept holds cables in place via a proprietary compartmental design and retention pins, which separate different types of cabling and, in many cases, eliminate the need for cable ties. Cable Stackers are secured to surfaces using two screws.

Short Description

Cable Stacker Mount, 3-Pocket, Screw Mount, PA66HIRHSUV, Black, 10/pkg

Global Part Name

CBLSTK3CZS-PA66HIRHSUV-BK

Length L (Imperial)

1.69

Length L (Metric)

43.0

Fixation Method

Screw Mounting and Rivet

Width W (Imperial)

1.42

Width W (Metric)

36.0

Height H (Imperial)

4.21

Height H (Metric)

106.9

Mounting Hole Diameter D (Imperial)

0.259

Mounting Hole Diameter D (Metric)

6.6 mm

Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Halogen Free	Yes
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +230°F (-40°C to +110°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	10
Package Quantity (Metric)	10
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

