

HDC-KIT-HE 48.150**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The wire connection level is designed as a screw element.

All screw connections are equipped with a wire protection spring.

Screw connection

General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HE, Size: 12, Poles: 48, Screw connection, 500 V, 16 A, diecast aluminium, PG
Order No.	1712550000
Type	HDC-KIT-HE 48.150
GTIN (EAN)	4008190947774
Qty.	1 pc(s).

HDC-KIT-HE 48.150

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	1,989.68 g
------------	------------

Temperatures

Limit temperature	-40 °C ... 100 °C
-------------------	-------------------

General data

BG	12	Cable glands	PG
Connection type PE	Screw connection	Material	diecast aluminium
Number of poles	48	Rated current (DIN EN 61984)	16 A
Rated voltage (DIN EN 61984)	500 V	Series	HE
Size	12		

Version

BG	12	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Material	diecast aluminium
Max. torque for main contact	0.55 Nm	Min. torque for main contact	0.5 Nm
Size	12	Surface finish	Powder coating
Type of connection	Screw connection		

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-01-90	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92
ECLASS 13.0	27-44-02-92	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	bfb1c983-6f18-4ba4-8907-38aad6aee076

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	Manufacturer's declaration
Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN