

HDC KIT HE 06.100 M**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

HDC kits are standardized kits for assembling complete plug-in connectors.

The HDC kits normally consist of a male insert, a female insert, a plug housing, a bulkhead housing and a cable gland.

Weidmüller offers a range of standard connector combinations with metric or PG cable entry threads.

The wire connection level is designed as a screw element.

All screw connections are equipped with a wire protection spring.

Screw connection

General ordering data

Version	RockStar® HDC kits-Heavy-duty connectors, Kit, HE, Size: 3, Poles: 6, Screw connection, 500 V, 24 A, diecast aluminium, M 20
Order No.	1802730000
Type	HDC KIT HE 06.100 M
GTIN (EAN)	4032248257348
Qty.	1 pc(s).

HDC KIT HE 06.100 M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	347.68 g
------------	----------

Temperatures

Limit temperature	-40 °C ... 100 °C
-------------------	-------------------

General data

BG	3	Cable glands	M 20
Connection type PE	Screw connection	Material	diecast aluminium
Number of poles	6	Rated current (DIN EN 61984)	24 A
Rated voltage (DIN EN 61984)	500 V	Series	HE
Size	3		

Version

BG	3	Conductor cross-section, max.	2.5 mm ²
Conductor cross-section, min.	0.5 mm ²	Material	diecast aluminium
Max. torque for main contact	0.55 Nm	Min. torque for main contact	0.5 Nm
Size	3	Surface finish	Powder coating
Type of connection	Screw connection		

Classifications

ETIM 6.0	EC002943	ETIM 7.0	EC002943
ETIM 8.0	EC002943	ETIM 9.0	EC002943
ETIM 10.0	EC002943	ECLASS 9.0	27-44-02-92
ECLASS 9.1	27-44-01-90	ECLASS 10.0	27-44-02-92
ECLASS 11.0	27-44-02-92	ECLASS 12.0	27-44-02-92
ECLASS 13.0	27-44-02-92	ECLASS 14.0	27-44-02-92
ECLASS 15.0	27-44-02-92		

Environmental Product Compliance

RoHS Compliance Status	Compliant with exemption
RoHS Exemption (if applicable/known)	6c
REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	bfb1c983-6f18-4ba4-8907-38aad6aee076

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN FL FIELDWIRING EN