

**AIMESA VRM 4,37****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

- for automatic stripping of individual wires
- stripping of flexible wires according to DIN VDE 0295, Cl. 5
- Partial stripping of insulation, the isolation remains on wire end
- Change of tools not necessary
- Quick and easy setting for the proper cross-section
- Electric drive

**General ordering data**

|            |                             |
|------------|-----------------------------|
| Version    | Accessories, Set of cutters |
| Order No.  | <a href="#">2007390000</a>  |
| Type       | AIMESA VRM 4,37             |
| GTIN (EAN) | 4050118392807               |
| Qty.       | 1 pc(s).                    |

**AIMESA VRM 4,37****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Technical data****Dimensions and weights**

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 26.8 mm | Depth (inches)  | 1.055 inch |
| Height     | 1.6 mm  | Height (inches) | 0.063 inch |
| Width      | 20 mm   | Width (inches)  | 0.787 inch |
| Net weight | 4 g     |                 |            |

**Classifications**

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC002778    | ETIM 7.0    | EC002778    |
| ETIM 8.0    | EC002778    | ETIM 9.0    | EC002778    |
| ETIM 10.0   | EC002778    | ECLASS 9.0  | 17-13-01-01 |
| ECLASS 9.1  | 17-13-01-02 | ECLASS 10.0 | 17-13-01-02 |
| ECLASS 11.0 | 17-13-01-01 | ECLASS 12.0 | 17-13-01-01 |
| ECLASS 13.0 | 17-13-01-01 | ECLASS 14.0 | 17-13-01-01 |
| ECLASS 15.0 | 17-13-01-01 |             |             |

**Environmental Product Compliance**

|                        |                       |
|------------------------|-----------------------|
| RoHS Compliance Status | Compliant             |
| REACH SVHC             | No SVHC above 0.1 wt% |

**Important note**

|                     |                                                             |
|---------------------|-------------------------------------------------------------|
| Product information | 1534740000 - Powerstripper AM 12 (up to serial number 2018) |
|---------------------|-------------------------------------------------------------|

**Approvals**

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

**Downloads**

|            |                                          |
|------------|------------------------------------------|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|------------------------------------------|