

CD-BO 60X120 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Similar to illustration**

The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Cable duct, 60 mm x 120 mm, 8.00 mm x 12.00 mm, 2000 mm
Order No.	2588910000
Type	CD-BO 60X120 8/12 GY
GTIN (EAN)	4050118601831
Qty.	16 m
Delivery status	This article will no longer be available in the future.
Available until	2025-12-31

CD-BO 60X120 8/12 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Height	60 mm	Height (inches)	2.362 inch
Width	120 mm	Width (inches)	4.724 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	1,031 g		

Temperatures

Operating temperature range	-5...60 °C
-----------------------------	------------

General information

Colour	grey	Flexible wiring duct	No
Floor rails	2	Halogen	Yes
Included in delivery	Cable duct, Lid	Lid	Yes
Material	PVC / lead-free	Non-tracking	Yes
Operating temperature range	-5...60 °C	Slit gap	12 mm
Slit width	8 mm	Standards	In accordance with DIN EN 50085
Type of mounting	when screwed in, With adhesive, Riveted	UL 94 flammability rating	V-0
Usable cross-section	6,390 mm ²	Version of side panel	slotted

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ETIM 9.0	EC000012
ETIM 10.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03	ECLASS 13.0	27-40-07-03
ECLASS 14.0	27-40-07-03	ECLASS 15.0	27-40-07-03

Approvals

Approvals



Approvals MAMID	https://mdcop.weidmueller.com/mediadelivery/rendition/900_319262/-T1z1mm-S800/
ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads




Catalogues	Catalogues in PDF-format
------------	--

CD-BO 60X120 8/12 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



CD-BO 60X120 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Accessories**Metric**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-LID 120 GY	Version
Order No.	2589990000	Cable duct cover, 120 mm
GTIN (EAN)	4050118600773	
Qty.	2 m	

Rivet and cover

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	EXRV 6.5	Version
Order No.	2562690000	Expanding rivet, 32 mm x
GTIN (EAN)	4050118571639	
Qty.	1,000 pc(s).	
Type	EXRV 4.5	Version
Order No.	2562700000	Expanding rivet, 27.5 mm x
GTIN (EAN)	4050118571622	
Qty.	1,000 pc(s).	
Type	CD-SCCV	Version
Order No.	2554000000	Cable duct screw cover
GTIN (EAN)	4050118564136	
Qty.	1,000 pc(s).	
Type	EXRV-T 6.5	Version
Order No.	2562710000	Expanding-rivet tool
GTIN (EAN)	4050118571615	
Qty.	4 pc(s).	
Type	EXRV-T 4.5	Version
Order No.	2562720000	Expanding-rivet tool
GTIN (EAN)	4050118571578	
Qty.	4 pc(s).	

CD-BO 60X120 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****T-Form**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RETT 40	Version
Order No.	2554090000	Cable duct T-form binder, 40 mm x 107 mm
GTIN (EAN)	4050118564211	
Qty.	40 pc(s).	
Type	CD-RETT 60	Version
Order No.	2554100000	Cable duct T-form binder, 60 mm x 107 mm
GTIN (EAN)	4050118564228	
Qty.	25 pc(s).	

Separator

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-SE 60	Version
Order No.	2553960000	Cable duct separator, 60 mm x
GTIN (EAN)	4050118564099	
Qty.	60 pc(s).	

CD-BO 60X120 8/12 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Accessories

Marking



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

Type	CD-LBH	Version
Order No.	2562850000	Cable duct tag rail holder, 30 mm x
GTIN (EAN)	4050118571691	
Qty.	150 pc(s).	
Type	CD-LB	Version
Order No.	2562680000	Cable duct tag rail, 15 mm x
GTIN (EAN)	4050118571646	
Qty.	150 pc(s).	
Type	CD-LBK	Version
Order No.	2554120000	Cable duct tag rail kit, 30 mm x
GTIN (EAN)	4050118564242	
Qty.	20 pc(s).	

Flat

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.



General ordering data

Type	CD-RET 100/120	Version
Order No.	2554060000	Cable duct binder, 2.8 mm x 126 mm
GTIN (EAN)	4050118564181	
Qty.	250 pc(s).	

CD-BO 60X120 8/12 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Accessories****Side arm**

Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

**General ordering data**

Type	CD-RETA	Version
Order No.	2554080000	Cable duct binder arm, 8 mm x 115.3 mm
GTIN (EAN)	4050118564204	
Qty.	100 pc(s).	