

AAM 35-185 YE FLASH**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Power feed-in**

Our wide range of W-Series terminal blocks with our WPD main line branch terminals, which are optimised to guarantee both convenience and space gains, ensures a secure and convenient connection at the power feed-in.

General ordering data

Version	Terminal marker, 23.5 x 12 mm, Pitch in mm (P): 12.00 yellow
Order No.	2635600000
Type	AAM 35-185 YE FLASH
GTIN (EAN)	4050118674545
Qty.	40 pc(s).

AAM 35-185 YE FLASH

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Depth	6.8 mm	Depth (inches)	0.268 inch
Height	23.5 mm	Height (inches)	0.925 inch
Width	12 mm	Width (inches)	0.472 inch
Net weight	0.425 g		

Temperatures

Operating temperature range	-40...100 °C
-----------------------------	--------------

Material data

Material	PA 6.6	Colour	yellow
UL 94 flammability rating	V-2		

Rating data IECEx/ATEX

Operating temperature range	-40...100 °C
-----------------------------	--------------

Dimensions

Pitch in mm (P)	12 mm
-----------------	-------

General

Operating temperature range, max.	100 °C	Operating temperature range, min.	-40 °C
-----------------------------------	--------	-----------------------------------	--------

Classifications

ETIM 6.0	EC000761	ETIM 7.0	EC000761
ETIM 8.0	EC000761	ETIM 9.0	EC000761
ETIM 10.0	EC000761	ECLASS 9.0	27-14-11-37
ECLASS 9.1	27-14-11-37	ECLASS 10.0	27-14-11-37
ECLASS 11.0	27-28-11-01	ECLASS 12.0	27-28-11-01
ECLASS 13.0	27-28-11-01	ECLASS 14.0	27-28-11-01
ECLASS 15.0	27-28-11-01		

Approvals

ROHS	Conform
------	---------

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

AAM 35-185 YE FLASH

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

