

IE-C5DE4UP0050PCSPCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**General ordering data**

Version	Dragline cable, M8 P-code - IP67 straight pin, M8 P-code - IP67 straight pin, Cat. 5e, PUR, 5 m
Order No.	2717780050
Type	IE-C5DE4UP0050PCSPCS-E
GTIN (EAN)	4050118780307
Qty.	1 pc(s).

IE-C5DE4UP0050PCSPCS-E**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Length	5 m	Length (inches)	196.85 inch
Net weight	319 g		

Temperatures

Operating temperature	-40 °C...80 °C
-----------------------	----------------

Technical specifications for cable

Bending cycles	2 Mio	Colour coding	white, yellow, blue, orange
Halogen	halogen-free, according to IEC 60754	Insulation	Polyolefin
Number of poles	4	Number of wires	4
Resistance to oils	in accordance with IEC 60811:404	Resistance to spread of flame	Yes
Sheath material	PUR	Sheathing colour	black
Shielded	Yes	Temperature range, moving	-30...70 °C
Temperature range, stationary	-40...80 °C	Test voltage: wire-wire-shield	1 kV DC, 1 min, 1000 V _{eff} , 50 Hz, 1 min

General technical data

Protection degree	IP67
-------------------	------

Plug, left

Plug left	M8, P-coded, IP67, male contact, straight, plug, Plastic, shielded
-----------	--

Plug, right

Plug right	M8, P-coded, IP67, male contact, straight, plug, Plastic, shielded
------------	--

Classifications

ETIM 6.0	EC002599	ETIM 7.0	EC002599
ETIM 8.0	EC002599	ETIM 9.0	EC002599
ETIM 10.0	EC002599	ECLASS 9.0	27-06-03-08
ECLASS 9.1	27-06-03-08	ECLASS 10.0	27-06-03-08
ECLASS 11.0	27-06-03-08	ECLASS 12.0	27-06-03-08
ECLASS 13.0	27-06-03-08	ECLASS 14.0	27-06-03-08
ECLASS 15.0	27-06-03-08		

Environmental Product Compliance

RoHS Compliance Status	Compliant
REACH SVHC	Lead 7439-92-1

Approvals

ROHS	Conform
------	---------

IE-C5DE4UP0050PCSPCS-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Catalogues

[Catalogues in PDF-format](#)

IE-C5DE4UP0050PCSPCS-E

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Drawings

Wiring

M12		M12
1	yellow	1
2	white	2
3	orange	3
4	blue	4