

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190360007](#)
Status: **Active**
Overview: [Snap Plugs and Receptacles](#)
Description: Avikrimp Snap Plug, for 14-16 AWG Wire, Mylar Tape, 24.31mm Length

Documents:	
3D Model	Product Specification PS-19902-011-001 (PDF)
Drawing (PDF)	Product Specification PS-19902-015-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E152602

General

Product Family	Quick Disconnects
Series	19036
Comments	Extruded Nylon Insulation
Crimp Quality Equipment	Yes
Insulated	Partial
Overview	Snap Plugs and Receptacles
Product Name	Avikrimp
Type	Snap Plug
UPC	800753048201

Physical

Barrel Type	Closed
Color - Resin	Blue
Flammability	94V-2
Gender	Male
Glow-Wire Capable	No
Insulation	Nylon (PA)
Lock to Mating Part	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.776/g
Orientation	Straight
Packaging Type	Adhesive Tape on Reel
Tab Thickness	N/A
Tab Width	N/A
Wire Insulation Diameter	4.30mm max.
Wire Size AWG	14, 16
Wire Size mm²	1.30-2.00

Electrical


Voltage - Maximum	N/A
-------------------	-----

Material Info

Engineering Number	B-879T
--------------------	--------

Reference - Drawing Numbers

Product Specification	PS-19902-011-001, PS-19902-015-001
Sales Drawing	SD-19036-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)4578-DC (25
June 2020)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[19036 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880085
Mini-Mac Applicator	638853400

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19036-0007