

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0351500400

Status:


Active

Overview:

VersaBlade Wire-to-Wire Connector System

Description:

VersaBlade Hybrid Receptacle Housing, without Mounting Ears, 4 Circuits, Natural



Documents:	
3D Model (PDF)	Application Specification 351500000ASKOR-000 (PDF)
Drawing (PDF)	Packaging Specification PK-35150-004-001 (PDF)
3D Model	Datasheet (PDF)
Product Specification PS-35150-003-001 (PDF)	Brochure (PDF)
Application Specification 351500000ASENG-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	35150
Application	Power, Wire-to-Wire
Overview	VersaBlade Wire-to-Wire Connector System
Product Name	VersaBlade
UPC	800753876804
Physical	
Breakaway	No
Circuits (maximum)	4
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	4.110/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	6.20mm
Pitch - Termination Interface	6.20mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +120°C
Material Info	
Reference - Drawing Numbers	
Application Specification	351500000AS_ENG-000, 351500000AS_KOR-000
Packaging Specification	PK-35150-004-001
Product Specification	PS-35150-003-001
Sales Drawing	SD-35150-0400-001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

35150 Series

Mates With

VersaBlade Plug Housing 35151

Use With

VersaBlade Crimp Terminals 35745 (ckt 1), 35747 (ckt 2), 35746 (ckt 3), 35748 (ckt 4)
VersaBlade TPA 351500290 , 351500292 , 351500293 , 351500294

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[35150-0400](#)