

Specification Sheet

Part Number: 151-04159

Temporarily holds wires along routing path until ready to make permanent.

Built-in CutZone safety feature prevents damage to wires and cables.

Unique EZ Feed slot maintains clear space to insert cable ties.



Frame mount allows for simple quarter-turn mounting into 80/20, 40-15 Series aluminum frames.

Cradle Mount With Frame Attachment, 0.24" Cradle Area, 0.7 x 0.31" Frame Mount, PA66STHS, Black, 100/Pkg

Article Number 151-04159

Type CTCM6CZF

Color Black (BK)

Quantity Per bag

Product Description

The cradle mount with frame attachment can be twisted into industrial frames with a 0.7 x 0.31" frame mount and is ideal for routing wires in industrial applications where rework and adjustments are common. Mount features a 0.24" cradle opening for cable retention. The cradle arms can temporarily hold wires for simple adjustments and cable additions and protect against abrasion and cable damage. To permanently mount the bundle, the EZ Feed cable tie slot eliminates common obstructions for faster completion. During rework, the CutZone prevents wire damage when cutting off cable ties.

Short Description	Cradle Mount With Frame Attachment, 0.24" Cradle Area, 0.7 x 0.31" Frame Mount, PA66STHS, Black, 100/Pkg
Global Part Name	CTCM6CZF-PA66STHS-BK
Length L (Imperial)	1.0
Length L (Metric)	25.4
Fixation Method	80/20 Frame
Width W (Imperial)	0.76
Width W (Metric)	19.3
Height H (Imperial)	0.55
Height H (Metric)	14.0
Cable Tie Width Max (Imperial)	0.36
Cable Tie Width Max (Metric)	9.07
Material	Polyamide 6.6, super tough, heat stabilized (PA66STHS)
Material Shortcut	PA66STHS
Flammability	UL 94 HB

Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	3926909988

About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. (www.hellermann.tyton.com).

© 2024 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)