

# FlexTrax®

## Overview

Amphenol Network Solutions introduces one of the most innovative and imaginative cable management solutions in the world! With easy assembly and installation, the 2" FlexTrax® is a flexible cable manager that enables quick access to cables for rapid changes in complex routing applications. The track design enables high visibility to cable management capacity and measures 2" x 2" x 1ft.

## Key Benefits

### Adaptable

- Snap multiple sections together to create any length
- Mounting accessories can attach to the rear or side walls for maximum versatility
- Can be trimmed to custom lengths with side-cutters

### Secure

- Multiple clamping options to a variety of surfaces
- Gates overlap to securely contain cables
- Detents hold gates in closed position
- Optional latch provides a positive locking latch

### Durable

- Strong, polypropylene material
- Flame extinguishing rating (UL94 V-0)
- Strong framework with high impact resistance
- Can be routed in complex paths
- Shape can be changed as needed

### Other Unique Benefits

- Gates can open and close when channel is flexed
- Patented design (see <http://amphenol-ns.com/patents>)
- Can be stretched or compressed to line up with existing holes
- Cables can exit through a hole or gates can be removed
- Easily see cables and available capacity



## Applications

FlexTrax® is suitable for a variety of indoor applications such as:

- Slotted duct replacement
- Split-tube replacement
- Vertical cable manager (on a 2-post rack or inside a 4-post cabinet)
- Desk cable management



## Ordering Information

| Part Number              | Description                       | Comments                                                                              |
|--------------------------|-----------------------------------|---------------------------------------------------------------------------------------|
| <a href="#">FLX2-1FT</a> | 2" FlexTrax 1' Section with Clips | Two pre-attached mounting clips have a hole for a screw, or can snap into the C-clamp |

FLX2-1FT



## Accessories

| Part Number                      | Description                                  | Comments                                                                         |
|----------------------------------|----------------------------------------------|----------------------------------------------------------------------------------|
| <a href="#">FLX2-END-CLAMP</a>   | 2" FlexTrax End Clamp                        | For use with thin flat surfaces                                                  |
| <a href="#">FLX2-C-CLAMP</a>     | 2" FlexTrax C-Clamp                          | Attaches to mounting clip on FLX2-1FT                                            |
| <a href="#">FLX2-LATCH-10</a>    | 2" FlexTrax Latch (10 pack)                  | Use one Latch per 1FT section or as needed                                       |
| <a href="#">FLX2-BRKT-KIT-10</a> | 2" FlexTrax L-Bracket Hardware Kit (10 pack) | Standard vertical spacing is every 10RU                                          |
| <a href="#">FLX2-EXIT-2</a>      | 2" FlexTrax Exit (2 Pack)                    | Recommended for extra protection at the end of a section or cut section          |
| <a href="#">FLX2-DROP</a>        | 2" FlexTrax Wire Basket Drop Kit – 1 Drop    | 1 drop kit includes drop attachment, 2 FlexTrax Exits, and 1 FlexTrax End Clamp. |
| <a href="#">FLX2-4DROP</a>       | 2" FlexTrax Wire Basket Drop Kit – 4 Drops   | 4 drop kit includes drop attachment, 4 FlexTrax Exits, and 5 zip ties            |

FLX2-END-CLAMP




FLX2-C-CLAMP



FLX2-LATCH-10



FLX2-BRKT-KIT-10



FLX2-EXIT-2



FLX2-DROP



FLX2-4DROP

