

BrightConnX™ FLT Series SMD Terminal Block

FLT TERMINAL BLOCKS PROVIDE DISCRETE WIRE CONNECTION TO A PCB

Amphenol's BrightConnX™ FLT Terminal Block is a surface mount device for discrete wire connection to a PCB for LED Modules and other applications.

- Provides simple and secure poke-in wire connection for easy termination
- Surface mount termination for pick and place
- Suitable for a range of wire gauges from 18AWG–24AWG
- Can be used with solid or stranded wires (with tinned end)
- Wide operating temperature range: -40°C to +105°C



FEATURES

- Available in 1, 2 & 3 Poles
- Accepts 18AWG–24AWG wire
- Poke-in wire termination
- Port to release wire
- SMT terminations
- LCP housings

BENEFITS

- Provides application flexibility and space savings for multiple positions
- Suitable for up to 7A per wire
- Easy installation and reliable connection
- Easy wire removal for rework or changes
- Easy pick and place assembly
- Rugged, high temperature capability

TECHNICAL INFORMATION

MATERIAL

- Housing: Liquid Crystal Polymer, White Color
- Contacts: Copper Alloy, plated with Tin

MECHANICAL PERFORMANCE

- Ingress Protection:
- IP20 Wire Size:
 - A. Solid Conductor: 18AWG
 - B. Stranded Conductor: 24AWG–20AWG Solid & Stranded with tinned end
- Wire cross section: \varnothing 1.10mm max.
- Mechanical Shock: As per EIA-364-27, Condition A
- Vibration: As per EIA-364-28, Condition VII, Letter D

ELECTRICAL PERFORMANCE

- Voltage Rating: 250V
- Current Rating: 7A (18AWG), 5A (20AWG), 3A (22AWG), 2A (24AWG),
- Dielectric Withstanding Voltage: 1500VAC for 1 minute
- Insulation Resistance: 500M Ω min @ 500VDC test voltage

PACKAGING

- Reels

SPECIFICATION

- Amphenol Product Specification: S6222C
- RoHS and REACH compliant

ENVIRONMENTAL

- Operating Temperature Range: -40°C to +105°C

APPROVALS AND CERTIFICATIONS

- UL 1977 (Pending)

TARGET MARKETS/APPLICATIONS



LED Lighting

PART NUMBERS

Description	Part Numbers
FLT Series SMD Terminal Blocks – 1 POLE	FLT-S12WR-00
FLT Series SMD Terminal Blocks – 2 POLE	FLT-S22WR-00
FLT Series SMD Terminal Blocks – 3 POLE	FLT-322WR-00