




# BELDEN Molded Cable Assemblies



NEW PRODUCT NEW PRODUCT NEW PRODUCT NEW PRODUCT



### 9-Position Shielded D-Subminiature Cable Assembly

Designed for RS-449 applications. Molded handles are 100% shielded to assist in FCC compliance and guard against EMI/RFI. All connectors tin-plated and male connectors have detents for positive ground connection. Wiring is point-to-point with the shield to connector shell. Jack screw retention on both connectors.

- 300V 80°C, UL AWM Style 2464
- Foil Shield

MOUSER STOCK NO.	Belden Part No.	Fig.	Gender	Length (feet)	Nom. O.D. (In.)	Price Each	
						1	5
<a href="#">566-49905A</a>	49905A	A	Male/Female	5	.244	54.85	49.79
<a href="#">566-49906A</a>	49906A	A	Male/Female	10	.244	61.09	55.43
<a href="#">566-49907A</a>	49907A	A	Male/Female	25	.244	75.54	68.54

### 37-Position Shielded D-Subminiature Cable Assembly

Designed for RS-449 applications where assembly is exposed to high noise environment. Molded handles are 100% shielded to assist in FCC compliance and guard against EMI/RFI. All connectors are tin-plated and male connectors have detents to allow for a positive shield to ground connection. Wiring is point-to-point with shield to connector shell and pin#1. Jack screw retention on both connectors.

- 300V 80°C, UL AWM Style 2464
- Foil Shield

MOUSER STOCK NO.	Belden Part No.	Fig.	Gender	Length (feet)	Nom. O.D. (In.)	Price Each	
						1	5
<a href="#">566-49950A</a>	49950A	C	Male/Male	5	.480	106.64	96.76
<a href="#">566-49951A</a>	49951A	C	Male/Male	10	.480	126.65	114.91
<a href="#">566-49955A</a>	49955A	C	Male/Female	5	.480	109.98	99.79
<a href="#">566-49956A</a>	49956A	C	Male/Female	10	.480	129.97	117.92
<a href="#">566-49957A</a>	49957A	C	Male/Female	25	.480	192.19	174.38

### 15-Position Shielded D-Subminiature Cable Assembly

Designed for RS-449 applications. Molded handles are 100% shielded to assist in FCC compliance and guard against EMI/RFI. All connectors tin-plated and male connectors have detents for positive ground connection. Wiring is point-to-point with the shield to connector shell. Jack screw retention on both connectors.

- 300V 80°C, UL AWM Style 2464
- Foil plus Braid Shield

MOUSER STOCK NO.	Belden Part No.	Fig.	Gender	Length (feet)	Nom. O.D. (In.)	Price Each	
						1	5
<a href="#">566-49745A</a>	49745A	B	Male/Female	5	.300	69.97	63.48
<a href="#">566-49746A</a>	49746A	B	Male/Female	10	.300	77.76	70.55
<a href="#">566-49747A</a>	49747A	B	Male/Female	25	.300	103.32	93.74

### 25-Position Shielded D-Subminiature Cable Assembly

Designed for RS-232 applications. Molded handles are 100% shielded to guard against EMI/RFI where indicated. All connectors are tin-plated and male connectors have detents to allow for a positive shield to ground connection. Wiring is point-to-point with the shield to connector shell. Jack screw retention on both connectors.

- 300V 80°C, UL AWM Style 2464
- Foil Shield

MOUSER STOCK NO.	Belden Part No.	Fig.	Gender	Length (feet)	Nom. O.D. (In.)	Price Each	
						1	5
<a href="#">566-49673A</a>	49673A	C	Male/Female	5	.339	72.20	65.51
<a href="#">566-49674A</a>	49674A	C	Male/Female	10	.339	88.87	80.63
<a href="#">566-49675A</a>	49675A	C	Male/Female	25	.339	116.65	105.83

- 300V 80°C, UL AWM Style 2464
- Foil plus Braid Shield

MOUSER STOCK NO.	Belden Part No.	Fig.	Gender	Length (feet)	Nom. O.D. (In.)	Price Each	
						1	5
<a href="#">566-49615A</a>	49615A	C	Male/Female	5	.370	75.54	68.54
<a href="#">566-49616A</a>	49616A	C	Male/Female	10	.370	87.76	79.63

### SCSI-1 Cable Assembly

Molded handles are 100% shielded to guard against EMI/RFI and assists in FCC compliance. These assemblies have tin-plated connectors and can be used in single-ended or differential configurations. Wiring is per SCSI standard

- 26AWG (7x34) Stranded tinned copper conductor
- 30V 80°C, UL AWM Style 2919

MOUSER STOCK NO.	Belden Part No.	Fig.	Gender	Length (feet)	Nom. O.D. (In.)	Price Each	
						1	5
<a href="#">566-49802A</a>	49802A	D	Male/Male	16.4	.535	137.76	124.99

### GPIB Cable Assembly

General Purpose Interface Bus Cable Assembly are used with electronic equipment that is IEEE-488 compatible. Molded connector is male/female design for easy stacking and comes with milled-in metric jack screws.

- 6 pairs 26 AWG (7x34), 10 singles 26AWG (7x34), 1 single 24AWG (7x32)
- 300V 80°C, UL AWM Style 2464
- Unshielded

MOUSER STOCK NO.	Belden Part No.	Fig.	Gender	Length (feet)	Nom. O.D. (In.)	Price Each	
						1	5
<b>Unshielded</b>							
<a href="#">566-49642</a>	49642	E	Male/Female	3.3	.350	125.54	113.90
<a href="#">566-49643</a>	49643	E	Male/Female	6.6	.350	131.08	118.92
<b>Shielded</b>							
<a href="#">566-49733</a>	49733	E	Male/Female	1.6	.350	131.08	118.92
<a href="#">566-49734</a>	49734	E	Male/Female	3.3	.350	134.42	121.96
<a href="#">566-49735</a>	49735	E	Male/Female	6.6	.350	141.08	128.00
<a href="#">566-49736</a>	49736	E	Male/Female	9.8	.350	147.74	134.05

NEW PRODUCT NEW PRODUCT NEW PRODUCT NEW PRODUCT