


PANDUIT Heat Stabilized and Metal Detectable Cable Ties



This product is RoHS compliant.



PANDUIT PAN-TY® NYLON GENERAL PURPOSE LOCKING CABLE TIES

- Engineered with quality features designed to increase productivity and reduce your total installed cost
- UL Listed
- No sharp edges
- Finger grip tip
- Bent tip



RoHS Compliant

Heat Stabilized Nylon 6/6 Black For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Fig.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each		
						1	100	500
Subminiature - Minimum Loop Tensile Strength: 8lbs.								
644-PLT.6SM-M30	PLT.6SM-M30	A	2.80	0.60	0.070	.09	.07	.06
Miniature - Minimum Loop Tensile Strength: 18lbs.								
644-PLT.7M-M30	PLT.7M-M30	A	3.10	0.680	0.090	.08	.06	.05
644-PLT1M-M30	PLT1M-M30	A	3.90	0.870	0.098	.08	.06	.05
644-PLT1.5M-M30	PLT1.5M-M30	A	5.60	1.250	0.098	.09	.08	.06
644-PLT2M-M30	PLT2M-M30	A	8.00	2.000	0.098	.10	.08	.06
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-PLT1.5I-M30	PLT1.5I-M30	A	5.60	1.38	0.142	.14	.10	.09
644-PLT2I-M30	PLT2I-M30	A	8.00	2.00	0.142	.13	.11	.09
644-PLT3I-M30	PLT3I-M30	A	11.40	3.00	0.145	.36	.33	.30
644-PLT4I-M30	PLT4I-M30	A	14.50	4.00	0.145	.54	.40	.33
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-PLT1S-M30	PLT1S-M30	A	4.80	1.00	0.190	.14	.12	.10
644-PLT1.5S-M30	PLT1.5S-M30	A	6.20	1.50	0.190	.18	.13	.11
644-PLT2S-M30	PLT2S-M30	A	7.40	1.88	0.190	.14	.12	.10
644-PLT2.5S-M30	PLT2.5S-M30	A	9.80	2.50	0.190	.43	.32	.27
644-PLT3S-M30	PLT3S-M30	A	11.50	3.00	0.190	.44	.40	.36
644-PLT4S-M30	PLT4S-M30	A	14.50	4.00	0.190	.52	.39	.33
644-PLT5S-M30	PLT5S-M30	A	17.50	5.00	0.190	.72	.54	.45

Heat Stabilized Weather Resistant Nylon 6/6 Black



RoHS Compliant

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Fig.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each		
						1	100	500
Miniature - Minimum Loop Tensile Strength: 18lbs.								
644-PLT1M-M300	PLT1M-M300	A	3.90	0.87	0.098	.12	.09	.08
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-PLT1.5I-M300	PLT1.5I-M300	A	5.60	1.38	0.142	.17	.13	.11
644-PLT2I-M300	PLT2I-M300	A	8.00	2.00	0.142	.17	.14	.12
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-PLT1S-M300	PLT1S-M300	A	4.00	1.00	0.19	.20	.15	.13
644-PLT2S-M300	PLT2S-M300	A	7.40	1.88	0.19	.17	.14	.12
644-PLT4S-M300	PLT4S-M300	A	14.50	4.00	0.19	.70	.53	.44

PANDUIT DOME-TOP® BARB TY CABLE TIES

- Features:**
- Stainless steel barb provides consistent performance and reliability
 - Curved tip
 - Low threading force
 - UL Listed
 - Dome-top head



RoHS Compliant

Heat Stabilized Nylon 6/6 Black For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Fig.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each		
						1	100	500
Miniature - Minimum Loop Tensile Strength: 18lbs.								
644-BT1M-M30	BT1M-M30	B	4.00	0.90	0.095	.09	.07	.06
644-BT1.5M-M30	BT1.5M-M30	B	6.30	1.50	0.095	.13	.09	.08
644-BT2M-M30	BT2M-M30	B	7.90	2.00	0.095	.12	.09	.07
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-BT1.5I-M30	BT1.5I-M30	B	6.10	1.50	0.141	.14	.10	.09
644-BT2I-M30	BT2I-M30	B	8.00	2.00	0.141	.17	.13	.11
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-BT2S-M30	BT2S-M30	B	8.00	2.00	0.185	.19	.14	.12
644-BT4S-M30	BT4S-M30	B	15.10	4.00	0.185	.40	.32	.28

PANDUIT PAN-TY® RELEASABLE CABLE TIES

- Features:**
- Heat stabilized material for high temperature applications up to 239°F (115°C) - indoor use
 - Extended release tab permits easy release and re-use where changes are anticipated during development, production or servicing in the field.
 - UL94V-2



RoHS Compliant

Heat Stabilized Nylon 6/6 Black For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Fig.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each		
						1	100	500
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-PR1.5S-M30	PR1.5S-M30	C	6.30	1.50	0.316	.31	.23	.20

© Copyright 2009 Mouser Electronics

CONTOUR-TY® CABLE TIES - LOW PROFILE

The low profile head and the parallel-entry design along with outside teeth on tie body make it the ideal tie for use in high vibration applications.

- Features:**
- Smooth round edges
 - Fully enclosed head
 - Curved tip and aggressive grip for fast and easy installation



RoHS Compliant

Heat Stabilized Nylon 6/6 Black For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Fig.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each		
						1	100	500
Miniature - Minimum Loop Tensile Strength: 18lbs.								
644-CBR1M-M30	CBR1M-M30	D	4.10	1.00	0.098	.12	.09	.07
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-CBR1.5I-M30	CBR1.5I-M30	D	5.90	1.50	0.14	.19	.14	.12
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-CBR2S-M30	CBR2S-M30	D	7.6	2.00	0.19	.25	.18	.15
644-CBR3S-M30	CBR3S-M30	D	10.8	3.00	0.19	.62	.46	.39
644-CBR4S-M30	CBR4S-M30	D	14.0	4.00	0.19	.71	.53	.44

HIGH TEMPERATURE PEEK PAN-TY® CABLE TIES

Ideal for use in high temperature and harsh chemical environments.

- Features:**
- Polyetheretherketone material (PEEK)
 - Halogen-free
 - Gamma radiation resistant
 - Operating temp range up to 500°F
 - Chemical resistant
 - Low water absorption
 - Good electrical isolation properties
 - Color - Translucent Brown
 - UL Flammability - UL94V-0



RoHS Compliant

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Fig.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each		
						1	100	500
644-PLT2S-M71	PLT2S-M71	E	7.40	1.88	0.19	2.47	1.85	1.55

PANDUIT SUPER-GRIP™ CABLE TIES

Are designed to withstand rough installation practices that occur in MRO and construction projects.

- Features:**
- Provide superior bundle tightness
 - Excellent tensile strength
 - Thin, wide strap body
 - Tapered tip with aggressive grips
 - Distinctive flared neck
 - Low profile design
 - Stronger bridge design
 - Relief on bottom of head



Heat Stabilized Nylon 6/6 Black For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Fig.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each		
						1	100	500
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-SG200S-M30	SG200S-M30	F	8.30	2.00	0.225	.15	.13	.107
644-SG300S-M30	SG300S-M30	F	12.40	3.20	0.225	.54	.41	.345

PAN-TY® METAL DETECTABLE CABLE TIES

Are designed to meet food, beverage, and pharmaceutical safety standards. Featuring metal impregnated material, these ties are identifiable by metal detectors and x-ray inspection equipment. Additionally, the distinct blue color of the ties facilitates quick visual detection in manufacturing environments.

- Features:**
- Metal impregnated material
 - Blue color
 - One-piece design with locking wedge
 - Curved, tapered tip
 - Smooth, round edges
 - Max operation temp: 185°F



RoHS Compliant

Metal Detectable Nylon 6/6 Black For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Panduit Part No.	Fig.	Length (in.)	Max. Bundle Dia. (in.)	Width (in.)	Price Each		
						1	100	500
Intermediate - Minimum Loop Tensile Strength: 40lbs.								
644-PLT2I-C86	PLT2I-C86	G	8.00	2.00	0.135	.64	.48	.40
Standard - Minimum Loop Tensile Strength: 50lbs.								
644-PLT2S-C86	PLT2S-C86	G	7.30	1.85	0.190	.53	.40	.33
644-PLT3S-C86	PLT3S-C86	G	11.50	3.00	0.190	1.08	.81	.67
644-PLT4S-C86	PLT4S-C86	G	14.40	4.00	0.190	1.22	.92	.77
Light/Heavy (Straight Tip) - Minimum Loop Tensile Strength: 120lbs.								
644-PLT3H-L86	PLT3H-L86	G	11.10	3.00	0.30	1.77	1.33	1.11
644-PLT4H-L86	PLT4H-L86	G	14.40	4.00	0.30	1.81	1.36	1.13

© Copyright 2009 Mouser Electronics

Wire & Cable Mgmt. Panduit