

BELDEN Hook-up Wire



This product is RoHS compliant.



PVC INSULATED HOOK-UP WIRE

PVC Hook-up Wire is Tinned Copper conducted and is PVC insulated. It is also flame and ozone resistant, as well as being inert to most chemicals, oils and solvents.

COLOR CODE CHART

Colors=Ordering Suffix

Brown=01	Lt. Blue=06	Tan=11
Red=02	Violet=07	Pink=12
Orange=03	Gray=08	Dk. Blue=13
Yellow=04	White=09	
Green=05	Black=10	

(Type B) MIL-W-16878/1-PVC (600V, 105°C)

To order replace ___ with applicable code for color desired.

Belden Part No.	Conductor		Nominal O.D. (in.)	MOUSER STOCK NO.	Stocked Colors	Price Per 100' Spool	MOUSER STOCK NO.	Stocked Colors	Price Per 1000' Spool
	AWG	Stranded							
8500	16	19x29	.079	566-8500-100-___	02, 04-06, 09, 10	55.64	566-8500-1000-___	01, 02, 05, 09, 10	384.42
8501	18	7x26	.068	566-8501-100-___	01-06, 09-10	44.51	566-8501-1000-___	02, 06, 09, 10	299.27
8502	20	7x28	.058	566-8502-100-___	01-10	38.25	566-8502-1000-___	01-06, 08-10	227.96
8503	22	7x30	.050	566-8503-100-___	01-10	31.52	566-8503-1000-___	04, 08-10	182.37
8504	24	7x32	.044	566-8504-100-___	01-06, 08-10	28.85	566-8504-1000-___	01-05, 08-10	167.22
8505	26	7x34	.039	566-8505-100-___	01-10	28.16	566-8505-1000-___	01-10	176.24

(Type MW) MIL-W-76C-PVC (1000V, 80°C)

8527	12	65x30	.128	566-8527-100-___	02-07, 09-10	135.46	566-8527-1000-___	02-10	694.44
8520	14	41x30	.111	566-8520-100-___	01-06, 09, 10	92.65	566-8520-1000-___	02, 03, 05, 06, 09, 10	420.88
8521	16	26x30	.098	566-8521-100-___	01-10	64.12	566-8521-1000-___	01-07, 10	260.02
8522	18	16x30	.080	566-8522-100-___	01-10	39.31	566-8522-1000-___	02, 03, 05, 06, 08-10	221.28
8523	20	10x30	.070	566-8523-100-___	01-10	38.78	566-8523-1000-___	02	196.15
8529	20	Solid	.066	566-8529-100-___	07-10	33.40	566-8529-1000-___	02-08, 10	193.30
8524	22	7x30	.064	566-8524-100-___	01-10	31.25	566-8524-1000-___	02, 04	159.52
8530	22	Solid	.059	566-8530-100-___	02-06, 09, 10	28.63	566-8530-1000-___	02, 06, 08, 10	162.53
8525	24	7x32	.058	566-8525-100-___	01-10	28.19	566-8525-1000-___		

UL AWM Style 1061 (300V, 80°C)

9984	24	7x32	.044	566-9984-100-___	02-05, 09-10	25.88	566-9984-1000-___	01-05, 10	154.02
9975	24	Solid	.040	566-9975-100-___	02, 10	16.90	566-9975-1000-___	10	92.80
9985	26	7x34	.039	566-9985-100-___	01-05, 08-10	23.39	566-9985-1000-___	02, 03, 09, 10, 13	143.97
9986	28	7x36	.035	566-9986-100-___	02-03, 09-10	21.89	566-9986-1000-___	02, 10	138.78
9987	30	7x38	.032	566-9987-100-___	09-10	23.39	566-9987-1000-___	02, 07, 09	151.34
9978	30	Solid	.030	566-9978-100-___	01-05, 07-10	21.97	566-9978-1000-___	02	136.78

UL AWM Style 1015 (600V, 105°C)

9910	10	65x28	.180	566-9910-100-___	02, 04, 09-10	226.06	566-9910-1000-___		
9912	12	65x30	.158	566-9912-100-___	01, 02, 04, 05, 09, 10	150.51	566-9912-1000-___		
8916	14	41x30	.138	566-8916-100-___	01-05, 09-10	88.23	566-8916-1000-___		
8917	16	26x30	.123	566-8917-100-___	01-05, 09, 10	65.08	566-8917-1000-___	02, 04, 05, 10, 13	485.81
8918	18	16x30	.110	566-8918-100-___	01-05, 09, 10	49.39	566-8918-1000-___	01-05, 09, 10, 13	329.83
8919	20	10x30	.100	566-8919-100-___	02, 04-05, 09, 10, 13	38.25	566-8919-1000-___	09, 13	263.03
8920	22	7x30	.093	566-8920-100-___	02-04, 09, 10	30.01	566-8920-1000-___	02, 03, 05, 10	206.18
9924	24	7x32	.088	566-9924-100-___			566-9924-1000-___	02, 03, 10, 13	186.12

Dual Rated UL AWM Style 1007 (300V, 80°C), (CSA Type TR-64, 90°C)

9916	16	26x30	.092	566-9916-100-___	01, 02, 04, 05, 07, 09, 10	60.16	566-9916-1000-___	03, 04, 08, 09, 13	400.98
9918	18	16x30	.079	566-9918-100-___	01-10	41.70	566-9918-1000-___	01-05, 07-09, 13	265.71
9919	20	7x28	.069	566-9919-100-___	01-02, 04-05, 07, 09, 10	37.41	566-9919-1000-___	01-05, 07-10, 13	223.28
9921	22	7x30	.062	566-9921-100-___	01-10	30.42	566-9921-1000-___	01-05, 07, 09, 13	170.22
9923	24	7x32	.056	566-9923-100-___	02, 09, 10	25.55	566-9923-1000-___	01-04, 08-10, 13	154.35
9926	26	7x34	.051	566-9926-100-___	02, 10	23.39	566-9926-1000-___	01-05, 08-10, 13	143.97
9928	28	7x36	.047	566-9928-100-___	01-10	21.89	566-9928-1000-___	02-05, 09, 10, 13	138.78

BELDEN HIGH-TEMPERATURE TEFLON® INSULATED HOOK-UP WIRE

Stranded Silver-Coated Copper conductor insulated with extruded TFE Teflon®.

COLOR CODE CHART

Colors=Ordering Suffix

Brown=01	Lt. Blue=06	Tan=11
Red=02	Violet=07	Pink=12
Orange=03	Gray=08	Dk. Blue=13
Yellow=04	White=09	
Green=05	Black=10	

UL AMW Style 1213 105°C MIL-W-16878/4 Teflon® 600V, 200°C

To order replace ___ with applicable code for color desired.

Belden Part No.	Conductor		Nominal O.D. (in.)	MOUSER STOCK NO.	Stocked Colors	Price Per 100' Spool	MOUSER STOCK NO.	Stocked Colors	Price Per 1000' Spool
	AWG	Stranded							
83008	20	7x28	.058	566-83008-100-___	01-06, 09, 10	46.49	566-83008-1000-___	02, 09, 10	358.51
83007	20	19x32	.058	566-83007-100-___	01-10	51.16	566-83007-1000-___	02, 04-06, 09-10	449.86
83006	22	19x34	.050	566-83006-100-___	01-10	42.83	566-83006-1000-___	02-06, 09, 10	352.54
83005	22	7x30	.050	566-83005-100-___	01-10	37.17	566-83005-1000-___	01-10	299.77
83004	24	7x32	.044	566-83004-100-___	01-10	30.42	566-83004-1000-___	09	240.32
83003	24	19x36	.044	566-83003-100-___	01-10	35.39	566-83003-1000-___	02-04, 06-10	295.43
83002	26	7x34	.039	566-83002-100-___	01-10	29.03	566-83002-1000-___	02, 06, 09	221.95
83000	30	7x38	.032	566-83000-100-___	01-10	25.55	566-83000-1000-___	04, 06	204.08

UL AWM Style 1371-105°C MIL-W-16878/4 Teflon® 600V, 200°C

83009	18	19x30	.068	566-83009-100-___	01-10	59.89	566-83009-1000-___	01, 06, 09	552.99
83010	16	19x29	.077	566-83010-100-___	01-10	77.74	566-83010-1000-___	03-05, 09, 10	675.38

UL AWM Style 1180 300V 200°C MIL-W-16878/5 Teflon® 1000V, 200°C

83030	16	19x29	.088	566-83030-100-___	01-10	88.12	566-83030-1000-___	02	770.38
83029	18	19x30	.078	566-83029-100-___	01-10	68.51	566-83029-1000-___	06, 09, 10	672.97
83028	20	7x28	.068	566-83028-100-___	01-06, 09, 10	51.96	566-83028-1000-___	02, 10	436.93
83027	20	19x32	.068	566-83027-100-___	01-10	60.16	566-83027-1000-___	02, 03, 06, 08-10	512.51
83026	22	19x34	.060	566-83026-100-___	01-10	48.51	566-83026-1000-___	01-04, 06, 08-10	403.31
83025	22	7x30	.060	566-83025-100-___	01-06, 09, 10	41.70	566-83025-1000-___	02, 03, 07, 09, 10	344.36
83023	24	19x36	.040	566-83023-100-___	01-10	39.99	566-83023-1000-___	02-05, 09, 10	357.18

