


BELDEN Computer and Instrumentation Cable



RoHS Compliant This product is RoHS compliant.



BELDEN OVERALL BELDFOIL® SHIELDED, INSTRUMENTATION, AND COMPUTER CABLE

• 24 AWG Stranded Conductors (7x32) • Tinned Copper, PVC Insulated, Twisted Pairs • UL AVM Style 2464 (300V 80°C), CSA AVM 1 A • Chrome PVC Jacket



RoHS Compliant

Belden Part No.	Fig.	Number of Pairs	Nominal O.D. (in.)	MOUSER STOCK NO.	Price Per 100' Spool	MOUSER STOCK NO.	Price Per 500' Spool	MOUSER STOCK NO.	Price Per 1000' Spool
9501	A	1	.156	566-9501-100	30.70	566-9501-500	128.37	566-9501-1000	227.92
9502	A	2	.222	566-9502-100	47.18	566-9502-500	201.64	566-9502-1000	374.67
9503	A	3	.232	566-9503-100	62.82	566-9503-500	265.21	566-9503-1000	497.70
9504	A	4	.265	566-9504-100	76.80	566-9504-500	321.04	566-9504-1000	569.69
9505	A	5	.289	566-9505-100	84.13	566-9505-500	335.55	566-9505-1000	681.30
9506	A	6	.289	566-9506-100	121.46	566-9506-500	503.81	-----	-----
9507	A	7	.294	566-9507-100	131.97	-----	-----	-----	-----
9508	A	8	.324	566-9508-100	141.84	566-9508-500	551.82	-----	-----
9509	A	9	.334	566-9509-100	166.78	-----	-----	-----	-----
9510	A	10	.368	566-9510-100	181.42	566-9510-500	758.43	-----	-----
9515	A	15	.417	566-9515-100	271.32	-----	-----	-----	-----
9519	A	19	.448	566-9519-100	375.19	-----	-----	-----	-----

BELDEN INDUSTRIAL AUTOMATION AND PROCESS CONTROL CABLES

Shielded, Instrumentation 300V Power-Limited Tray Cables

• Tinned Copper, Twisted Pairs • Overall 100% Beldfoil® Shield • Flame Retardant PVC Insulation and PVC Jacket • Chrome Jacket Color



RoHS Compliant

Belden Part No.	Fig.	Number of Pairs	Nominal O.D. (in.)	AWG (Stranded)	MOUSER STOCK NO.	500' Spool	MOUSER STOCK NO.	500' Unreel Box	MOUSER STOCK NO.	1000' Spool	MOUSER STOCK NO.	1000' Unreel Box
9322	B	1	.200	22 (7 x 30)	-----	-----	-----	-----	-----	-----	566-9322-1000U	320.22
9512	B	2	.310	22 (7 x 30)	566-9512-500	300.31	-----	-----	566-9512-1000	584.17	-----	-----
9513	B	3	.324	22 (7 x 30)	566-9513-500	383.11	-----	-----	-----	-----	-----	-----
9514	B	4	.356	22 (7 x 30)	566-9514-500	514.57	-----	-----	-----	-----	-----	-----
9516	B	6	.418	22 (7 x 30)	566-9516-500	747.60	-----	-----	-----	-----	-----	-----
9316	C	1	.256	16 (19 x 29)	-----	-----	566-9316-500U	368.97	-----	-----	-----	-----
9320	C	1	.217	20 (19 x 32)	-----	-----	566-9320-500U	233.02	-----	-----	-----	-----
9365	D	1	.245	18 (19 x 30)	-----	-----	566-9365-500U	446.34	-----	-----	-----	-----

BELDEN BLUEHOSE® CABLES

RoHS Compliant

Belden Part No.	Fig.	Description	AWG	Stranding	Nom. O.D. (in.)	Nom. Imp.	% Type Shield	MOUSER STOCK NO.	Price Per 100' Spool	MOUSER STOCK NO.	Price Per 500' Spool	MOUSER STOCK NO.	Price Per 1000' Spool
9463	E	Twinaxial, Foil / Braid Shield	20	7 x 28	.238	78	100	566-9463-100	73.25	566-9463-500	303.81	566-9463-1000	585.80

Unshielded, Instrumentation 300V Power-Limited Tray Cables

• Flame Retardant PVC Insulation and PVC Jacket • Chrome Jacket Color

Belden Part No.	Fig.	Number of Pairs	Nominal O.D. (in.)	AWG (Stranded)	MOUSER STOCK NO.	Price Per 500' Unreel Box	MOUSER STOCK NO.	Price Per 1000' Unreel Box
9407	F	1	.198	22 (7 x 30)	566-9407-500U	136.65	-----	-----
9410	F	1	.254	16 (19 x 29)	566-9410-500U	329.40	-----	-----

BELDEN INFINITY® CABLES

Belden Infinity® Cables are a complete line specifically designed to handle the rigorous speeds and near constant motion encountered in automated equipment such as robots, pick-and-place machines, automatic handling systems, multi-axis machine tools, and conveyor systems.

• Reduced Cable Memory • Greater Flex Life • Greater System Uptime • No Talc Problems



RoHS Compliant

* All parts Non-Shielded except for part 7436AS which is 85% Braid Shielded

Belden Part No.	Fig.	Number of Conductors	Nominal O.D. (in.)	AWG (Stranded)	MOUSER STOCK NO.	Price Per 250' Spool	MOUSER STOCK NO.	Price Per 500' Spool	MOUSER STOCK NO.	Price Per 1000' Spool
FCC (1mm Flex Life)										
7400A	G	2	.240	20 (10 x 30)	566-7400A-250-08	101.52	566-7400A-500-08	193.78	566-7400A-1000-08	401.16
7401A	G	3	.250	20 (10 x 30)	566-7401A-250-08	136.95	566-7401A-500-08	273.91	566-7401A-1000-08	547.82
7402A	G	4	.275	20 (10 x 30)	566-7402A-250-08	167.91	566-7402A-500-08	335.82	566-7402A-1000-08	671.64
7403A	G	5	.300	20 (10 x 30)	566-7403A-250-08	202.73	566-7403A-500-08	405.46	566-7403A-1000-08	810.92
7404A	G	7	.345	20 (10 x 30)	566-7404A-250-08	281.77	566-7404A-500-08	563.54	566-7404A-1000-08	1127.08
7409A	G	2	.264	18 (16 x 30)	566-7409A-250-08	142.33	566-7409A-500-08	277.94	566-7409A-1000-08	555.89
7410A	G	3	.280	18 (16 x 30)	566-7410A-250-08	167.91	566-7410A-500-08	324.55	566-7410A-1000-08	671.64
7411A	G	4	.305	18 (16 x 30)	566-7411A-250-08	220.11	566-7411A-500-08	440.23	566-7411A-1000-08	880.47
7412A	G	5	.330	18 (16 x 30)	566-7412A-250-08	277.90	566-7412A-500-08	555.81	566-7412A-1000-08	1111.62
7413A	G	7	.385	18 (16 x 30)	566-7413A-250-08	387.30	566-7413A-500-08	756.39	566-7413A-1000-08	1512.79
7415A	G	12	.475	18 (16 x 30)	566-7415A-250-08	708.27	566-7415A-500-08	1374.03	566-7415A-1000-08	2748.06
7416A	G	18	.560	18 (16 x 30)	566-7416A-250-08	945.68	566-7416A-500-08	1891.37	-----	-----
7417A	G	25	.696	18 (16 x 30)	566-7417A-250-08	1320.15	566-7417A-500-08	2640.30	-----	-----
7422A	G	3	.305	16 (26 x 30)	566-7422A-250-08	274.08	566-7422A-500-08	548.16	566-7422A-1000-08	1096.34
7423A	G	4	.330	16 (26 x 30)	566-7423A-250-08	353.16	566-7423A-500-08	686.32	566-7423A-1000-08	1412.67
7424A	G	5	.360	16 (26 x 30)	566-7424A-250-08	390.16	-----	-----	566-7424A-1000-08	1783.44
7428A	G	18	.650	16 (26 x 30)	566-7428A-250-08	1503.39	566-7428A-500-08	3006.78	-----	-----
7436A	G	4	.395	14 (41 x 30)	566-7436A-250-08	511.50	566-7436A-500-08	1023.01	566-7436A-1000-08	1895.65
*7436AS	G	4	.482	14 (41 x 30)	566-7436AS-250-08	1488.10	566-7436AS-500-08	2976.21	-----	-----
C-TC+ (9mm Flex Life)										
7101A	H	3	.275	20 (74 x 38)	566-7101A-250-03	694.83	566-7101A-500-03	1389.66	566-7101A-1000-03	2779.32

