


MILL-MAX In-line Sockets and Headers



DIMENSIONS: in.



Sockets

Mill-Max

.100" INTERCONNECTS

Plating		
Code	Shell	Inner Contact
10	10µ" Gold	n/a
43	200µ" Tin (Matte Fin.)	30µ" Gold
93	200µ" Tin/Lead	30µ" Gold

- May be cut to length
- Tail Type: Solder

* Not RoHS Compliant



Single Row

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Mill-Max Part No.	Fig.	Description	No. of Cont.	Price Each		
					1	10	100
.018" Dia. Pins, 3A							
575-010064	800-10-064-10-001000	A	Straight Header	64	8.64	8.24	6.12
575-643506	399-10-164-10-009000	B	Rt. Angle Header	64	9.98	9.52	7.06
575-642001	800-10-064-20-001000	C	Rt. Angle Socket	64	10.71	10.21	7.58
*575-643903	399-93-164-10-003000	C	Rt. Angle Socket	64	11.34	10.81	8.02
575-39943164	399-43-164-10-003000	C	Rt. Angle Socket	64	11.34	10.81	8.02
575-640006	350-10-164-00-106000	D	Surf. Mt. Header	64	9.17	7.94	6.40
.030" Dia. Pins, 4.5A							
*575-010064	800-10-064-10-001000	E	Straight Header	64	9.04	8.63	6.41
*575-093050	801-93-050-10-001000	F	Straight Socket	50	7.87	7.52	5.57
575-8014305010	801-43-050-10-001000	F	Straight Socket	50	8.27	7.89	5.86
575-642001	800-10-064-20-001000	G	Rt. Angle Header	64	10.29	9.82	7.29
*575-502001	801-93-050-20-001000	H	Rt. Angle Socket	50	10.22	9.76	7.23
575-8014305020	801-43-050-20-001000	H	Rt. Angle Socket	50	10.71	10.22	7.59
575-641002	800-10-064-10-002000	I	Low Prof. Header	64	8.63	8.24	6.11
*575-641012	801-93-064-10-002000	J	Low Prof. Socket	64	9.18	8.75	6.49
575-8014306410	801-43-064-10-002000	J	Low Prof. Socket	64	9.52	9.08	6.73

© Copyright 2009 Mouser Electronics

Single Row (Cont.)

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Mill-Max Part No.	Fig.	Description	No. of Cont.	Price Each		
					1	10	100
.030" Dia. Pins, 4.5A (cont.)							
*575-361012	801-93-036-10-012000	K	Low Prof. Socket	36	5.34	5.10	3.78
575-80143036	801-43-036-10-012000	K	Low Prof. Socket	36	5.62	5.37	3.98

Double Row

For quantities of 500 and up, call for quote.

MOUSER STOCK NO.	Mill-Max Part No.	Fig.	Description	No. of Cont.	Price Each		
					1	10	100
.030" Dia. Pins, 4.5A							
575-641022	802-10-064-10-002000	L	Low Prof. Header	2x32	6.81	6.07	4.91
*575-721022	803-93-072-10-002000	M	Low Prof. Socket	2x36	8.18	7.29	5.91
575-80343072102	803-43-072-10-002000	M	Low Prof. Socket	2x36	8.49	7.57	6.13
575-641001	802-10-064-10-001000	N	Straight Header	2x32	9.14	8.72	6.48
575-642201	802-10-064-20-001000	O	Rt. Angle Header	2x32	13.86	13.24	9.82
*575-072101	803-93-072-10-001000	P	Straight Socket	2x36	8.95	8.00	6.47
575-80343072101	803-43-072-10-001000	P	Straight Socket	2x36	9.37	8.37	6.78
*575-100201	803-93-100-20-001000	Q	Rt. Angle Socket	2x50	18.33	16.36	13.26
575-8034310020	803-43-100-20-001000	Q	Rt. Angle Socket	2x50	19.35	17.28	14.00

© Copyright 2009 Mouser Electronics

