

# KEYSTONE LED Holders and Spacer Mounts



## “SNAP-IN” T-1 & T-1 3/4 LED HOLDERS

This product is RoHS compliant.

\* Material: Nylon 6/6, Black

For quantities of 2000 and up, call for quote.

MOUSER STOCK NO.		Fig.	LED Size	Color	Mounting Hole Size	Min. Mounting Center	Panel Thickness	Price Each			
Mfr.	Mfr. Part No.							1	100	500	1000
534-8309		A	T-1	0.114	0.232	0.188	0.171	.21	.18	.17	.13
534-8310		B	T-1 3/4	0.20	0.315	0.274	0.25	.21	.18	.17	.13

## “UNIVERSAL” SPACER MOUNTS FOR TRI-LEAD T-1(3MM) & T-1 3/4 (5MM)

\* Unique design separate leads and retains Tri-Lead (and/or Bi-Lead) components  
 \* Designed for PC board mounting of Tri-Lead (and/or Bi-Lead) T-1 and T-1 3/4 LEDs  
 \* Provides height control, lead retention and stability

\* Also suitable for mounting lamps, resistors, transistors, diodes, capacitors, etc.  
 \* Material: Black PVC, UL Rated 94V-0

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.		Fig.	Length "L"	Price Each			MOUSER STOCK NO.		Length "L"	Price Each		
Mfr.	Mfr. Part No.			1	100	500	Mfr.	Mfr. Part No.		1	100	500
534-8900		C	0.120	.22	.12	.10	534-8916	0.40	.22	.12	.11	
534-8901		C	0.140	.22	.14	.12	534-8917	0.42	.22	.14	.11	
534-8902		C	0.160	.22	.12	.10	534-8918	0.44	.18	.12	.10	
534-8903		C	0.180	.22	.12	.10	534-8919	0.45	.22	.12	.11	
534-8904		C	0.200	.22	.12	.10	534-8920	0.46	.22	.12	.11	
534-8905		C	0.220	.21	.13	.11	534-8921	0.48	.22	.12	.11	
534-8906		C	0.240	.22	.14	.12	534-8922	0.50	.25	.14	.13	
534-8907		C	0.250	.09	.08	.07	534-8923	0.55	.22	.14	.12	
534-8908		C	0.260	.22	.12	.10	534-8924	0.60	.22	.14	.12	
534-8909		C	0.280	.22	.14	.11	534-8925	0.65	.22	.14	.12	
534-8910		C	0.300	.22	.12	.10	534-8926	0.70	.22	.14	.12	
534-8911		C	0.320	.22	.14	.12	534-8927	0.75	.22	.14	.12	
534-8912		C	0.340	.23	.13	.11	534-8928	0.80	.22	.16	.12	
534-8913		C	0.350	.23	.13	.11	534-8929	0.85	.23	.16	.12	
534-8914		C	0.360	.23	.13	.11	534-8930	0.90	.23	.16	.12	
534-8915		C	0.380	.22	.14	.12	534-8931	0.95	.23	.16	.12	

## “SELF-ALIGNING” SPACER MOUNTS FOR BI-LEAD T-1(3MM) & T-1 3/4(5MM)

The spacer features an internally tapered barrier which guides the leads and eliminates the possibility of crimping and shorting. The internal configuration also assures positive self-alignment on .100 centers.

\* No special tools required  
 \* Cost and labor saving

\* Material: Natural Nylon  
 \* UL Rated 94V-2

MOUSER STOCK NO.		Fig.	Length "L"	"A" Ref	Price Each		
Mfr.	Mfr. Part No.				1	100	500
<b>T-1 3/4</b>							
534-8311		D	0.120	0.045	.18	.10	.09
534-8312		D	0.140	0.065	.18	.10	.09
534-8313		D	0.160	0.085	.18	.10	.09
534-8314		D	0.180	0.105	.18	.10	.09
534-8315		D	0.200	0.125	.18	.10	.09
534-8316		D	0.220	0.145	.18	.10	.09
534-8317		D	0.240	0.045	.18	.10	.09
534-8318		D	0.250	0.060	.18	.09	.08
534-8319		D	0.260	0.065	.18	.10	.09
534-8320		D	0.280	0.090	.18	.09	.08
534-8321		D	0.300	0.110	.18	.10	.09
534-8322		D	0.320	0.120	.18	.09	.07
534-8323		D	0.340	0.140	.18	.09	.08
534-8324		D	0.350	0.150	.18	.10	.09
534-8325		D	0.360	0.160	.18	.10	.09
534-8326		D	0.380	0.060	.18	.10	.09
534-8327		D	0.40	0.08	.18	.10	.09
534-8328		D	0.42	0.10	.18	.10	.09
534-8329		D	0.44	0.12	.18	.10	.09
534-8330		D	0.45	0.12	.18	.10	.09
534-8331		D	0.46	0.14	.18	.10	.09
534-8332		D	0.48	0.15	.18	.10	.09
534-8333		D	0.50	0.06	.18	.10	.09
534-8334		D	0.55	0.10	.18	.10	.09
534-8335		D	0.60	0.15	.18	.10	.09
534-8336		D	0.65	0.08	.18	.10	.09
534-8337		D	0.70	0.12	.18	.10	.09
534-8338		D	0.75	0.06	.18	.10	.09
534-8339		D	0.80	0.11	.18	.10	.09
534-8340		D	0.85	0.16	.18	.12	.10
534-8341		D	0.90	0.20	.18	.10	.09
534-8342		D	0.93	0.23	.18	.11	.09
<b>T-1</b>							
534-7351		E	0.120	0.045	.18	.10	.09
534-7352		E	0.140	0.065	.18	.09	.08
534-7353		E	0.160	0.085	.18	.14	.12
534-7354		E	0.180	0.105	.18	.10	.08
534-7355		E	0.200	0.125	.18	.14	.12
534-7356		E	0.220	0.145	.18	.11	.09
534-7357		E	0.240	0.045	.18	.14	.12
534-7358		E	0.250	0.060	.18	.10	.09
534-7359		E	0.260	0.065	.18	.14	.12
534-7360		E	0.280	0.090	.18	.10	.09
534-7361		E	0.300	0.110	.18	.11	.09
534-7362		E	0.320	0.120	.18	.10	.09
534-7363		E	0.340	0.140	.18	.10	.09
534-7364		E	0.350	0.150	.18	.10	.09
534-7365		E	0.360	0.160	.18	.11	.09
534-7366		E	0.380	0.060	.18	.10	.09
534-7367		E	0.40	0.08	.18	.10	.09
534-7368		E	0.42	0.10	.18	.10	.09
534-7369		E	0.44	0.12	.18	.10	.09
534-7370		E	0.45	0.12	.22	.14	.12
534-7371		E	0.46	0.14	.22	.10	.09
534-7372		E	0.48	0.15	.18	.10	.09
534-7373		E	0.50	0.06	.18	.10	.09
534-7374		E	0.55	0.10	.18	.10	.09
534-7375		E	0.60	0.15	.18	.10	.09
534-7376		E	0.65	0.08	.18	.10	.09
534-7377		E	0.70	0.12	.18	.10	.09
534-7378		E	0.75	0.06	.18	.10	.09
534-7379		E	0.80	0.11	.18	.10	.09
534-7380		E	0.85	0.16	.18	.10	.09
534-7381		E	0.90	0.20	.18	.10	.09
534-7382		E	0.93	0.23	.18	.10	.09

