

# MEDER Reed Switches



This product is RoHS compliant.



## MEDER REED SWITCHES

### Features:

- High breakdown voltage
- Super ultra-miniature
- Super ultra-miniature SMD
- High power
- Miniature high-performance
- Miniature offset -type
- Long life
- Miniature wide differential
- Miniature offset-type long reed



RoHS Compliant

For quantities of 250 and up, call for quote.

MOUSER STOCK NO.	Meder Part No.	Dimensions			Switched Power (W)	Description	Price Each			
		A	B	C			1	25	50	100
<a href="#">876-KSK-1A35-1015</a>	KSK-1A35-1015	10.5mm	0.71	34.5	20	1 Form A, 10.5mm AT 1015	.69	.671	.634	.605
<a href="#">876-KSK-1A35-1520</a>	KSK-1A35-1520	10.5mm	0.71	34.5	20	1 Form A, 10.5mm AT 1520	.60	.577	.539	.511
<a href="#">876-KSK-1A52-2025</a>	KSK-1A52-2025	21.1mm	0.108	55.2	50	1 Form A, 21mm AT 2025	1.29	1.22	1.15	1.10
<a href="#">876-KSK-1A52-3040</a>	KSK-1A52-3040	21.1mm	0.108	55.2	50	1 Form A, 21mm AT 3040	1.29	1.22	1.15	1.10
<a href="#">876-KSK-1A66-1015</a>	KSK-1A66-1015	14mm	0.087	44.1	10	1 Form A, 14mm AT 1015	.63	.60	.57	.54
<a href="#">876-KSK-1A66-1520</a>	KSK-1A66-1520	14mm	0.087	44.1	10	1 Form A, 14mm AT 1520	.63	.60	.57	.54
<a href="#">876-KSK-1A66-2030</a>	KSK-1A66-2030	14mm	0.087	44.1	10	1 Form A, 14mm AT 2030	.76	.72	.68	.64
<a href="#">876-KSK-1A80-1015</a>	KSK-1A80-1015	7mm	0.071	35.6	10	1 Form A, 7mm AT 1015	.93	.88	.83	.79
<a href="#">876-KSK-1A80-1520</a>	KSK-1A80-1520	7mm	0.071	35.6	10	1 Form A, 7mm AT 1520	.93	.88	.83	.79
<a href="#">876-KSK-1A80-2030</a>	KSK-1A80-2030	7mm	0.071	35.6	10	1 Form A, 7mm AT 2030	1.31	1.24	1.17	1.11
<a href="#">876-KSK-1A81-0510</a>	KSK-1A81-0510	13.5mm	0.071	35.6	10	1 Form A, 13.5mm AT 0510	.70	.67	.63	.60
<a href="#">876-KSK-1A85-2025</a>	KSK-1A85-2025	21.0mm	0.108	55.5	100	1 Form A, 21mm AT 2025	1.31	1.24	1.17	1.11
<a href="#">876-KSK-1A85-2030</a>	KSK-1A85-2030	21.0mm	0.108	55.5	100	1 Form A, 21mm AT 2030	1.31	1.24	1.17	1.11
<a href="#">876-KSK-1A85-2530</a>	KSK-1A85-2530	21.0mm	0.108	55.5	100	1 Form A, 21mm AT 2530	1.31	1.24	1.17	1.11
<a href="#">876-KSK-1A85-3040</a>	KSK-1A85-3040	21.0mm	0.108	55.5	100	1 Form A, 21mm AT 3040	1.31	1.24	1.17	1.11
<a href="#">876-KSK-1A87-1015</a>	KSK-1A87-1015	10.0mm	0.079	35.5	10	1 Form A, 10mm AT 1015	.74	.70	.66	.63
<a href="#">876-KSK-1A87-1520</a>	KSK-1A87-1520	10.0mm	0.079	35.5	10	1 Form A, 10mm AT 1520	.81	.772	.728	.695
<a href="#">876-KSK-1A87-2030</a>	KSK-1A87-2030	10.0mm	0.079	35.5	10	1 Form A, 10mm AT 2030	.74	.70	.66	.63
<a href="#">876-KSK-1C90U-1015</a>	KSK-1C90U-1015	14.0mm	0.100	56.1	20	1 Form C, 14mm AT 1015 Straight Lead	2.72	2.58	2.44	2.31
<a href="#">876-KSK-1C90U-1520</a>	KSK-1C90U-1520	14.0mm	0.100	56.1	20	1 Form C, 14mm AT 1520 Straight Lead	2.72	2.58	2.44	2.31
<a href="#">876-KSK-1C90F-1015</a>	KSK-1C90F-1015	14.0mm	0.100	54.5	20	1 Form C, 14mm AT 1015 Formed Lead	2.97	2.82	2.67	2.52
<a href="#">876-KSK-1C90F-1520</a>	KSK-1C90F-1520	14.0mm	0.100	54.5	20	1 Form C, 14mm AT 1520 Formed Lead	2.97	2.82	2.67	2.52
<a href="#">876-KSK-1C90F-2025</a>	KSK-1C90F-2025	14.0mm	0.100	54.5	20	1 Form C, 14mm AT 2025 Formed Lead	2.82	2.68	2.54	2.40
<a href="#">876-ORD211-1015</a>	ORD211-1015	10.0mm	0.6	44.1	24	1 Form A, 10mm AT 1015 OKI	.56	.53	.50	.48
<a href="#">876-ORD211-1520</a>	ORD211-1520	10.0mm	0.6	44.1	24	1 Form A, 10mm AT 1520 OKI	.56	.53	.50	.48
<a href="#">876-ORD211-2030</a>	ORD211-2030	10.0mm	0.6	44.1	24	1 Form A, 10mm AT 2030 OKI	.56	.53	.50	.48
<a href="#">876-ORD213-1015</a>	ORD213-1015	7.0mm	0.3	35.8	24	1 Form A, 7mm AT 1015 OKI	.82	.78	.74	.70
<a href="#">876-ORD213-1520</a>	ORD213-1520	7.0mm	0.3	35.8	24	1 Form A, 7mm AT 1520 OKI	.82	.78	.74	.70
<a href="#">876-ORD213-2030</a>	ORD213-2030	7.0mm	0.3	35.8	24	1 Form A, 7mm AT 2030	.84	.79	.75	.71
<a href="#">876-ORD213S-1-1015</a>	ORD213S-1-1015	10.2mm	0.5	1.8	24	1 Form A, Surface Mount 10.2mm AT 1015 OKI	1.16	1.11	1.05	.99
<a href="#">876-ORD213S-1T-1015</a>	ORD213S-1T-1015	10.2mm	0.5	1.8	24	1 Form A, Surface Mount 10.2mm AT 1015 T/R OKI	1.24	1.18	1.12	1.05
<a href="#">876-ORD219-1015</a>	ORD219-1015	12.0mm	0.5	44.3	100	1 Form A, 12mm AT 1015 OKI	.50	.48	.45	.43
<a href="#">876-ORD2210V-2025</a>	ORD2210V-2025	21.0mm	0.6	55.4	100	1 Form A, 21mm AT 2025 OKI	.95	.90	.859	.809
<a href="#">876-ORD2210V-2530</a>	ORD2210V-2530	21.0mm	0.6	55.4	100	1 Form A, 21mm AT 2530 OKI	.94	.89	.85	.80
<a href="#">876-ORD2211-2030</a>	ORD2211-2030	16.5mm	0.6	44.1	100	1 Form A, 16.5mm AT 2030 OKI	.80	.75	.70	.67
<a href="#">876-ORD2212-2030</a>	ORD2212-2030	16.5mm	0.21	44.1	100	Re 1 Form A, 16.5mm AT 2030 OKI	.95	.902	.853	.805
<a href="#">876-ORD2220-2030</a>	ORD2220-2030	14.0mm	0.5	56.7	40	1 Form A, 14mm AT 2030 OKI	.80	.76	.72	.68
<a href="#">876-ORD2221-2030</a>	ORD2221-2030	13.0mm	0.21	44.2	100	1 Form A, 13mm AT 2030 OKI	1.10	1.05	.99	.94
<a href="#">876-ORD228S-1-1015</a>	ORD228S-1-1015	14.0mm	0.5	19.6	100	1 Form A, Surface Mount 14mm AT 1015 OKI	.60	.57	.54	.51
<a href="#">876-ORD228S-1T-1015</a>	ORD228S-1T-1015	14.0mm	0.5	19.6	100	1 Form A, Surface Mount 14mm AT 1015 T/R OKI	.70	.67	.63	.60
<a href="#">876-ORD228VL-1015</a>	ORD228VL-1015	14.0mm	0.5	44.3	100	1 Form A, 14mm AT 1015 OKI	.44	.42	.40	.37
<a href="#">876-ORD228VL-1520</a>	ORD228VL-1520	14.0mm	0.5	44.3	100	1 Form A, 14mm AT 1520 OKI	.44	.42	.40	.37
<a href="#">876-ORD228VL-2030</a>	ORD228VL-2030	14.0mm	0.5	44.3	100	Form A, 14mm AT 2030 OKI	.47	.456	.434	.402
<a href="#">876-ORD229-2025</a>	ORD229-2025	21.0mm	0.6	55.4	50	1 Form A, 21mm AT 2025 OKI	.80	.76	.72	.68
<a href="#">876-ORD311-1015</a>	ORD311-1015	7.0mm	0.33	35.8	10	1 Form A, 7mm AT 1015 OKI	1.00	.95	.90	.85
<a href="#">876-ORD312-1015</a>	ORD312-1015	12.0mm	0.5	44.3	30	1 Form A, 12mm AT 1015 OKI	.84	.80	.76	.71
<a href="#">876-ORD9215-1015</a>	ORD9215-1015	17.0mm	0.5	44.1	10	1 Form A, 17mm AT 1015 OKI	.58	.51	.45	.38
<a href="#">876-ORD9215-1520</a>	ORD9215-1520	17.0mm	0.5	44.1	10	1 Form A, 17mm AT 1520 OKI	.58	.51	.45	.38
<a href="#">876-ORD9216-1015</a>	ORD9216-1015	14.0mm	0.5	44.3	10	1 Form A, 14mm AT 1015 OKI	.40	.38	.36	.34
<a href="#">876-ORD9216-1520</a>	ORD9216-1520	14.0mm	0.5	44.3	10	1 Form A, 14mm AT 1520 OKI	.40	.38	.36	.34
<a href="#">876-ORD9216-2030</a>	ORD9216-2030	14.0mm	0.5	44.3	10	1 Form A, 14mm AT 2030 OKI	.40	.38	.36	.34
<a href="#">876-ORT551-1015</a>	ORT551-1015	14.0mm	0.5	56.1	3	1 Form C, 14mm AT 1015 OKI	1.64	1.56	1.48	1.39
<a href="#">876-ORT551-1-1015</a>	ORT551-1-1015	14.0mm	0.5	56.1	3	1 Form C, 14mm, AT 1015 Formed Leads OKI	1.80	1.71	1.62	1.53