

KEYSTONE Mounting Brackets, Handles, & Accessories



KEYSTONE




MOUNTING BRACKETS

RoHS Compliant

For quantities of 1000 and up, call for quote.

MOUSER STOCK NO.	Fig.	Dimensions: in.								Material	Plating	Price Each			
		A	B	C	D	E	F	G Dia.	H Dia.			1	100	500	
Clear Hole Universal Brackets - Non-Threaded															
534-633	A1	.375	.375	.281	.218	.218	.032	.140	.140	Brass	Nickel	.14	.08	.07	
534-613	A1	.390	.453	.375	.234	.299	.032	.128	.147	Brass	Nickel	.26	.21	.18	
534-615	A1	.420	.343	.281	.281	.203	.032	.125	.144	Brass	Tin	.16	.10	.09	
534-4335	A1	.562	.562	.500	.412	.411	.062	.120	.120	Steel	Nickel	.32	.18	.16	
534-4336	A1	.562	.562	.500	.412	.412	.062	.144	.144	Steel	Nickel	.29	.18	.16	
534-618	A1	.628	.628	.375	.378	.378	.050	.169	.169	Brass	Nickel	.55	.28	.25	
534-619	A1	.687	.687	.375	.500	.500	.032	.144	.144	Steel	Tin	.28	.17	.15	
534-4326	A1	1.013	.487	.312	.816	.332	.050	.140	.140	Steel	Nickel	.44	.25	.22	
534-620	A1	1.156	.656	.375	.906	.406	.032	.169	.169	Steel	Tin	.31	.25	.22	
Clear Hole Board Brackets															
534-4325	B	---	---	---	---	---	---	---	---	Steel	Nickel	.50	.29	.26	
534-1564	C	---	---	---	---	---	---	---	---	Steel	Nickel	.52	.29	.26	
Threaded Brackets															
534-612	A2	.343	.375	.250	.203	.250	.062	4-40	.130	Steel	Zinc	.22	.13	.11	
534-621	A2	.343	.375	.250	.203	.250	.062	4-40	4-40	Steel	Zinc	.36	.21	.16	
534-616	A2	.453	.312	.250	.265	.187	.047	4-40	.136	Brass	Tin	.45	.33	.28	
534-630	D	---	---	---	---	---	---	---	---	Brass	Tin	1.17	.67	.62	
534-631	E	---	---	---	---	---	---	---	---	Steel	Tin	.60	.33	.27	
534-634	A2	.375	.375	.281	.218	.218	.032	6-32	.140	Brass	Nickel	.50	.28	.23	
534-614	A1	.420	.343	.312	.250	.197	.032	6-32	.144	Brass	Tin	.24	.15	.13	
534-4334	A2	.562	.562	.500	.412	.412	.062	6-32	6-32	Steel	Nickel	.87	.45	.364	
534-4332	F	---	---	---	---	---	---	6-32	---	Brass	Nickel	1.00	.50	.43	
534-4333	F	---	---	---	---	---	---	8-32	---	Brass	Nickel	1.20	.60	.49	
534-617	A1	.578	.500	.500	.328	.299	.062	6-32	.165	Steel	Tin	.45	.32	.28	
534-611	A1	.375	.422	.312	.234	.250	.037	8-32	.135	Brass	Tin	.64	.37	.32	
534-708	G	---	---	---	---	---	---	---	---	Steel	Nickel	1.00	.57	.50	



KEYSTONE ROUND INSTRUMENTATION HANDLES


• Enhance the look of quality products and equipment while providing sturdiness for contemporary equipment.

For quantities of 1000 and up, call for quote.



RoHS Compliant

Fig.	Dimensions: in.						Nickel Plated Brass				Aluminum Black Anodize					
	A	B	C Dia.	D	E	F	MOUSER STOCK NO.	1	10	100	500	MOUSER STOCK NO.	1	10	100	500
A	1.250	1.000	.156	.375	4-40	.156	534-7140	3.15	2.97	2.71	2.53	534-7170	2.52	2.32	2.26	2.12
A	2.000	1.000	.156	.375	4-40	.156	534-7141	3.71	3.10	2.89	2.70	534-7171	3.18	2.94	2.74	2.59
A	3.000	1.000	.156	.375	4-40	.156	534-7142	2.93	2.87	2.69	2.32	534-7172	2.94	2.74	2.53	2.21
A	1.250	.625	.187	.156	4-40	.187	534-9100	3.65	3.10	2.89	2.62	534-9110	3.45	3.27	3.11	2.95
A	1.500	.625	.187	.156	4-40	.187	-----	-	-	-	-	534-9111	2.61	2.43	2.26	2.04
A	1.500	.750	.187	.250	4-40	.187	534-9104	3.73	3.11	2.94	2.76	534-9114	2.86	2.61	2.47	2.28
A	1.750	.625	.187	.156	4-40	.187	534-9102	3.43	2.86	2.64	2.26	-----	-	-	-	-
A	2.000	.625	.187	.156	4-40	.187	-----	-	-	-	-	534-9113	3.19	2.69	2.50	2.34
A	1.250	1.000	.187	.250	6-32	.187	534-9106	3.85	3.23	3.05	2.87	534-9116	3.17	2.65	2.49	2.15
A	1.500	1.000	.187	.250	6-32	.187	534-9107	4.08	3.45	3.27	3.13	534-9117	3.49	2.92	2.71	2.50
A	2.000	1.000	.187	.250	6-32	.187	534-9108	3.56	3.33	3.09	2.84	534-9118	3.10	2.71	2.56	2.35
A	3.000	1.000	.187	.250	6-32	.187	534-9109	3.65	3.42	3.18	3.02	534-9119	3.10	2.71	2.56	2.35
A	3.000	1.500	.250	.562	8-32	.250	534-7143	3.80	3.56	3.30	3.12	534-7173	3.42	3.02	2.81	2.60
A	3.000	1.750	.250	.562	8-32	.250	534-485	4.20	3.50	3.25	2.77	534-515	3.34	2.91	2.76	2.48
A	3.500	1.500	.250	.562	8-32	.250	534-480	4.62	4.38	4.15	3.92	534-510	3.34	3.22	2.99	2.76
A	4.000	1.500	.250	.562	8-32	.250	534-7144	4.07	3.57	3.36	3.19	534-7174	3.51	3.29	3.03	2.90
A	4.000	1.750	.250	.562	8-32	.250	534-486	4.64	3.93	3.64	3.22	534-516	3.60	3.14	2.72	2.55
A	4.500	1.500	.250	.562	8-32	.250	534-481	4.78	4.03	3.73	3.27	534-511	3.52	3.22	2.99	2.76
A	4.500	1.750	.250	.562	8-32	.250	534-487	4.61	3.86	3.56	3.39	-----	-	-	-	-
A	5.000	1.500	.250	.562	8-32	.250	534-482	4.27	3.62	3.36	3.01	534-512	4.28	3.59	3.39	3.09
A	5.000	1.750	.250	.562	8-32	.250	534-488	4.78	4.09	3.88	3.68	534-518	4.39	3.87	3.68	3.31
A	5.500	1.500	.250	.562	8-32	.250	-----	-	-	-	-	534-513	4.50	3.79	3.54	3.20
A	6.000	1.500	.250	.562	8-32	.250	-----	-	-	-	-	534-514	4.66	4.09	3.69	3.23
A	6.000	1.750	.250	.562	8-32	.250	534-489	4.62	3.80	3.55	3.25	534-519	4.66	4.09	3.88	3.49
A	3.000	1.500	.312	.562	10-32	.312	534-7145	4.36	4.10	3.81	3.42	534-7175	3.88	3.64	3.33	3.08
A	4.000	1.500	.312	.562	10-32	.312	534-7146	4.61	4.26	4.04	3.48	534-7176	4.51	4.13	3.88	3.59
A	4.000	1.750	.312	.562	10-32	.312	534-493	4.44	3.96	3.78	3.47	534-523	4.05	3.79	3.48	3.24
A	4.500	1.500	.312	.562	10-32	.312	-----	-	-	-	-	534-520	4.18	4.01	3.71	3.43
A	4.500	1.750	.312	.562	10-32	.312	534-494	4.75	3.99	3.72	3.52	534-524	4.88	4.30	3.77	3.33
A	4.562	1.500	.312	.562	10-32	.312	534-7147	5.00	4.42	4.14	3.75	534-7177	4.40	3.66	3.42	3.32
A	5.000	1.500	.312	.562	10-32	.312	534-491	4.84	4.57	4.34	4.12	534-521	4.30	4.03	3.68	3.41
A	5.000	1.750	.312	.562	10-32	.312	534-495	5.35	4.48	4.12	3.91	534-525	4.41	4.26	4.05	3.65
A	5.500	1.500	.312	.562	10-32	.312	534-492	5.41	4.56	4.29	3.74	534-522	4.49	3.91	3.71	3.34
A	6.000	1.500	.312	.562	10-32	.312	534-7148	5.20	4.80	4.52	4.06	534-7178	4.81	4.03	3.64	3.41
A	6.000	1.750	.312	.562	10-32	.312	-----	-	-	-	-	534-526	4.65	4.05	3.75	3.49
A	6.437	1.750	.312	.562	10-32	.312	534-7149	5.91	4.99	4.59	4.13	534-7179	4.51	3.80	3.51	3.16
A	4.000	1.375	.375	.375	10-32	.375	534-7150	5.39	4.56	4.22	3.96	534-7180	3.89	3.65	3.36	3.19
A	6.000	1.375	.375	.375	10-32	.375	534-7151	4.90	4.56	4.18	3.80	534-7181	4.57	4.09	3.75	3.48



Keystone Hardware

KEYSTONE FERRULES FOR ROUND HANDLES

• To protect and support panel surface

RoHS Compliant

For quantities of 1000 and up, call for quote.

Fig.	Dimensions: in.						Nickel Plated Brass				Aluminum Black Anodize						
	For Diameter Thread	A	B	C Dia.	D	E	F	MOUSER STOCK NO.	1	10	100	500	MOUSER STOCK NO.	1	10	100	500
B	.156 / 4-40	.250	.120	.047	.125	.200	.161	534-7162	.78	.64	.55	.49	534-7192	1.07	.89	.75	.64
B	.187 / 4-40	.312	.120	.062	.125	.265	.203	534-9120	.97	.81	.69	.58	534-9122	1.23	1.18	1.00	.86
B	.187 / 6-32	.312	.144	.062	.125	.265	.203	534-9121	.85	.71	.60	.51	534-9123	1.25	.98	.87	.81
B	.250 / 8-32	.375	.170	.062	.187	.320	.260	534-7163	.85	.71	.60	.51	534-7193	1.25	1.08	.90	.77
B	.312 / 10-32	.562	.196	.062	.250	.406	.320	534-7164	1.30	1.13	1.01	.93	534-719				