


Pure Lead and Sealed Lead Acid Batteries



EnerSys PURE LEAD RECHARGEABLE BATTERIES

- High-Rate Power Density
- Capable of more than 300 Cycles
- High Stable Voltage Delivery
- Wide Temperature Range:
Cyclon Single Cells: -65°C ~ +80°C
Monobloc: -40°C ~ +40°C
- Fast Recharge: up to 95% Recharge in Less Than One Hour
- Maintains Performance and Physical Parameters in Extreme Conditions
- Can be mounted and operated in any position
- Provides the Longest Service Life Possible
- Low Self-Discharge Rate
- Rugged Construction

Cyclon 2 Volt Single Cells

For quantities of 50 and up, call for quote.

| MOUSER STOCK NO. | Energys Part No. | Fig. | Size | Capacity (Ah) | Dimensions: in. | | | | | Price Each | | | |
|------------------|------------------|------|------|---------------|-----------------|--------|-------------------|---------------|-------------|------------|-------|-------|-------|
| | | | | | Diameter | Height | Height Over Term. | Weight (lbs.) | Tabs | 1 | 5 | 10 | 25 |
| 846-0810-0004 | 0810-0004 | A | D | 2.5 | 1.35 | 2.41 | 2.68 | 0.39 | .187 x 0.25 | 10.23 | 9.38 | 8.87 | 8.48 |
| 846-0800-0004 | 0800-0004 | A | X | 5.0 | 1.75 | 2.87 | 3.21 | 0.80 | .250 x .025 | 15.08 | 13.86 | 13.04 | 12.63 |


Cyclon 4 and 6 Volt Monoblocs

For quantities of 50 and up, call for quote.

| MOUSER STOCK NO. | Energys Part No. | Fig. | Size | Capacity (Ah) | Dimensions: in. | | | | | Price Each | | | |
|------------------|------------------|------|------|---------------|-----------------|--------|-------------------|---------------|--------------|------------|-------|-------|-------|
| | | | | | Diameter | Height | Height Over Term. | Weight (lbs.) | Tabs | 1 | 5 | 10 | 25 |
| 4 Volt | | | | | | | | | | | | | |
| 846-0819-0010 | 0819-0010 | B | D | 2.5 | 3.13 | 1.81 | 2.75 | 0.8 | 0.187 x .025 | 18.59 | 17.09 | 16.08 | 15.08 |
| 846-0809-0010 | 0809-0010 | B | X | 5.0 | 3.80 | 2.12 | 3.02 | 1.62 | 0.250 x .025 | 28.77 | 26.44 | 24.88 | 23.33 |
| 846-0859-0010 | 0859-0010 | B | E | 8.0 | 3.81 | 2.13 | 4.00 | 2.11 | 0.250 x .025 | 24.55 | 22.88 | 22.57 | 22.11 |
| 6 Volt | | | | | | | | | | | | | |
| 846-0819-0012 | 0819-0012 | C | D | 2.5 | 4.48 | 1.81 | 2.75 | 1.15 | 0.187 x .025 | 26.73 | 24.57 | 23.12 | 21.68 |
| 846-0809-0012 | 0809-0012 | C | X | 5.0 | 5.48 | 2.12 | 3.02 | 2.16 | 0.250 x .025 | 32.65 | 31.77 | 30.01 | 28.24 |
| 846-0859-0012 | 0859-0012 | C | E | 8.0 | 5.48 | 2.13 | 4.00 | 3.15 | 0.250 x .025 | 41.73 | 38.24 | 36.05 | 33.65 |

Panasonic SEALED LEAD-ACID BATTERIES

- High Quality and Reliability
- Exceptional Deep Discharge Recover
- No Corrosive Gas Generation
- Long Service Life
- Quick Chargeability
- High Power Density
- Maintenance-Free Operation



For quantities of 10 and up, call for quote.

| MOUSER STOCK NO. | Panasonic Part No. | Nominal Voltage | Capacity 20 Hr. Rate (Ah) | Terminal Type | Dimensions: in. | | | Weight (lbs.) | Cycle Use | | Trickle Use | | Price Each |
|------------------|--------------------|-----------------|---------------------------|---------------|-----------------|------|------|---------------|-----------------|---------------|-----------------|---------------|------------|
| | | | | | L | W | H | | Initial Current | Control Volt. | Initial Current | Control Volt. | |
| 658-LCR061R3P | LC-R061R3P | 6 | 1.3 | .187" Faston | 3.82 | 0.95 | 1.97 | 0.66 | 0.52A | 7.25-7.45V | 0.195A | 6.8-6.9V | 15.87 |
| 658-LCR063R4PU | LC-R063R4PU | 6 | 3.4 | .187" Faston | 5.28 | 1.34 | 2.36 | 1.37 | 1.36A | 14.5-14.9V | 0.51A | 13.6-13.8V | 26.45 |
| 658-LCR064R5P | LC-R064R5P | 6 | 4.5 | .187" Faston | 2.76 | 1.89 | 4.02 | 1.59 | 1.80A | 7.25-7.45V | .675A | 6.8-6.9V | 15.84 |
| 658-LCR067R2P | LC-R067R2P | 6 | 7.2 | .187" Faston | 5.95 | 1.34 | 3.70 | 2.78 | 2.88A | 7.25-7.45V | 1.08A | 6.8-6.9V | 23.66 |
| 658-LCR067R2P1 | LC-R067R2P1 | 6 | 7.2 | .250" Faston | 5.95 | 1.34 | 3.70 | 2.78 | 2.88A | 7.25-7.45V | 1.08A | 6.8-6.9V | 23.66 |
| 658-LCR0612P | LC-R0612P | 6 | 12.0 | .187" Faston | 5.95 | 1.97 | 3.70 | 4.30 | 4.8A | 7.25-7.45V | 1.8A | 6.8-6.9V | 27.41 |
| 658-LCR0612P1 | LC-R0612P1 | 6 | 12.0 | .250" Faston | 5.95 | 1.97 | 3.70 | 4.30 | 4.8A | 7.25-7.45V | 1.8A | 6.8-6.9V | 27.41 |
| 658-LCR121R3PU | LC-R121R3PU | 12 | 1.3 | .187" Faston | 3.82 | 1.87 | 1.97 | 1.30 | 4.8A | 7.25-7.45V | 1.8A | 6.8-6.9V | 32.56 |
| 658-LCR122R2PU | LC-R122R2PU | 12 | 2.2 | .187" Faston | 6.97 | 1.34 | 2.36 | 1.76 | 0.88A | 14.5-14.9V | 0.33A | 13.6-13.8V | 34.21 |
| 658-LCR123R4PU | LC-R123R4PU | 12 | 3.4 | .187" Faston | 5.28 | 2.64 | 2.36 | 2.65 | 1.36A | 14.5-14.9V | 0.51A | 13.6-13.8V | 44.97 |
| 658-LCR127R2P | LC-R127R2P | 12 | 7.2 | .187" Faston | 5.95 | 2.54 | 3.70 | 5.45 | 2.88A | 14.5-14.9V | 1.08A | 13.6-13.8V | 39.26 |
| 658-LCR127R2P1 | LC-R127R2P1 | 12 | 7.2 | .250" Faston | 5.95 | 2.54 | 3.70 | 5.45 | 2.88A | 14.5-14.9V | 1.08A | 13.6-13.8V | 39.26 |
| 658-LCRD1217P | LC-RD1217P | 12 | 17.0 | Nut and Bolt | 7.13 | 2.99 | 6.57 | 14.34 | 6.8A | 14.5-14.9V | 2.55A | 13.6-13.8V | 93.35 |
| 658-LCLA1233P | LC-LA1233P | 12 | 33.0 | Nut and Bolt | 7.70 | 5.12 | 6.10 | 26.50 | 13.2A | 14.5-14.9V | 4.95A | 13.6-13.8V | 139.86 |

BK PRECISION BATTERY CAPACITY ANALYZER

Applications:
The need for battery maintenance tools is growing for use in Automotive, Field Service and Maintenance, Telecommunications, and UPS Manufacturing/Maintenance applications. Perfect instrument for anyone working with UPS systems, Emergency back-up Flood Lights, Home and Business Security Alarm Systems, or for any applications using a 12 volt lead acid battery.

- Specifications:**
- Measures both No Load Voltage and Battery Capacity
 - Displays storage capacity of 12V lead acid batteries as a percentage
 - Powered by battery under test

For quantities of 5 and up, call for quote.

| MOUSER STOCK NO. | B & K Part No. | Max Input Volt | Dimensions: in. | | | Weight (lbs) | Cap. Display Range | Price Each |
|------------------|----------------|----------------|-----------------|------|------|--------------|--------------------|------------|
| | | | W | H | D | | | |
| 615-600 | 600 | 20V | 3.14 | 6.30 | 1.60 | 2.20 | 0-100% | 319.00 |
| 615-601 | 601 | 20V | 3.14 | 9.50 | 1.60 | 2.30 | 0-100% | 419.00 |
| 615-602 | 602 | 50V | 3.14 | 9.50 | 1.60 | 2.30 | 0-100% | 425.00 |

