


Pliers, Cutters and Fuse Pullers



COOPER Hand Tools PLIERS



- Lightweight, miniature plier line
- Choice of oval, tapered, relieved, and angled head
- Full flush or semi-flush cutting edges
- Needle nose styles include long, short, curved, flat, and round to handle most forming, looping, twisting, insertion, and pickup jobs

- Forged from high quality alloy steel for maximum strength and durability
- Precision ground to close tolerances, individually finished and tested to ensure exact fit of jaws
- Polished heads with gun metal handles
- Made in the U. S. A.

Xcelite® Diagonal Cutting Pliers and Electronic Shears

† Not ESD Safe


For quantities of 6 and up, call for quote.

Xcelite® Electronic Pliers

For quantities of 6 and up, call for quote.

| MOUSER STOCK NO. | | Fig. | Size (in.) | Description | Price Each |
|------------------|---------------|------|------------|---|------------|
| Mfr. | Mfr. Part No. | | | | |
| 578—SN54 | | A | 5 | Long nose with side cutter, finely scored jaws | 17.65 |
| 578—SN55 | | A | 5 1/2 | Long nose with side cutter, finely scored jaws | 18.35 |
| 578—L4 | | B | 4 | Long nose subminiature, very fine point | 14.32 |
| 578—LN54 | | B | 5 | Long nose finely scored jaws | 15.71 |
| 578—LN55 | | B | 5 1/2 | Long nose finely scored jaws | 16.15 |
| 578—CN54G | | C | 5 | Long curved nose (approx 60°), smooth jaws | 17.65 |
| 578—NN54 | | B | 5 | Needle nose finely scored jaws | 18.49 |
| 578—NN54G | | B | 5 | Needle nose smooth jaws, slightly rounded edges | 19.55 |
| 578—RN54 | | B | 4 1/2 | Round nose smooth jaws, for forming loops in wire | 16.87 |
| 578—NN7776 | | B | 6 | Extra long needle nose | 17.62 |
| 578—DN54G | | D | 5 | Flat nose smooth jaws | 14.36 |
| 578—LN54G | | B | 5 | Thin long nose smooth jaws | 15.83 |

| MOUSER STOCK NO. | | Fig. | Size (in.) | Description | Price Each |
|------------------|---------------|------|------------|--|------------|
| Mfr. | Mfr. Part No. | | | | |
| 578—MS54J | | E | 4 | Tapered head, flush cut | 15.90 |
| 578—MS54 | | F | 4 | Oval head, flush cut | 16.18 |
| 578—S54S | | F | 4 | Oval head, semi-flush cut | 14.36 |
| 578—S55 | | F | 4 1/2 | Diagonal cutting gen. purpose, 7/16" cutting blade | 16.87 |
| 578—MS54J | | F | 5 | Diagonal cutting gen. purpose, 5/8" cutting blade | 16.16 |
| 578—GA54 | | E | 4 | Relieved tapered head, flush cut | 16.34 |
| 578—MS549J | | G | 4 | Angled diagonal end cutter at 29° | 26.73 |
| 578—S475JS | | E | 4 | Tapered head, diagonal cut | 16.62 |
| 578—54CG | | E | 5 | Tapered head flush cut | 15.58 |
| 578—170M | | F | 4 | Diagonal pliers standard beveled edges, red grips | 18.80 |
| 578—C1 | | H | 5 | Shear/cutter blue grips | 6.83 |
| | | I | - - - | Includes MS54, SN54, LN54, NN54, plus 4" traverse end cutter, 4" flat nose pliers & leather pouch w/ brass snaps | 109.56 |



/// eagle PC BOARD "DREAM" TOOLS
plastic devices

Small, lightweight pliers. Designed primarily for holding, bending, and cutting fine wires in electronic, radio, TV, and electrical work.

- Take a look at what these pliers can do

For quantities of 5 and up, call for quote.

| MOUSER STOCK NO. | | Fig. | Size (in.) | Description | Price Each |
|------------------|---------------|------|------------|---|------------|
| Mfr. | Mfr. Part No. | | | | |
| 383—1001 | | A | 4 1/2 | Lead Forming: forms strain reliefs in component leads and indents in leads to hold components during wave soldering | 30.86 |
| 383—1002 | | B | 4 1/2 | Lead Bending: for adjusting lead spacing on small components | 30.86 |
| 383—1003 | | C | 5 1/2 | Bent Nose: manipulates & dresses components in tight spaces | 30.21 |
| 383—1004 | | D | 5 | Nippers: very narrow cutting head for cutting in close spaces | 28.62 |
| 383—1005 | | E | 5 | Tip Cutters: for those crowded, inconvenient areas | 28.62 |
| 383—1006 | | F | 5 1/4 | End Cutting Nippers: "top down" cutting for high density areas | 38.16 |

/// eagle FUSE PULLERS
plastic devices

| MOUSER STOCK NO. | | Fig. | Description | Price Each | | | |
|------------------|---------------|------|------------------|------------|-----|-----|-----|
| Mfr. | Mfr. Part No. | | | 1 | 5 | 10 | 20 |
| 441—EPD213 | | G | Dual Fuse Puller | .48 | .39 | .35 | .31 |
| 441—EPD223 | | H | Dual Fuse Puller | .59 | .49 | .46 | .43 |
| 441—EPD224 | | I | Dual Fuse Puller | .54 | .44 | .41 | .37 |

PLATO® PLATOSHEAR LEAD CUTTERS

- Effortless shearing action, comfort, light weight, and safety for electronics lead cutting
- Platoshear requires 50% less operator effort and has a longer cutting life than conventional cutters because it shears rather than bites
- Cushioned handles provide daylong comfort
- Thin profile designed for those hard-to-get-at areas in electronic assembly where conventional cutters can't reach
- Made in the U.S.A.

For quantities of 6 and up, call for quote.

| MOUSER STOCK NO. | | Fig. | Description | Price Each |
|------------------|---------------|------|--|------------|
| Mfr. | Mfr. Part No. | | | |
| 577—170 | | J | General purpose Lead Cutter | 5.57 |
| 577—170SD | | K | Static Dissipative Lead cutter | 11.03 |
| 577—175SD | | K | Static Dissipative Lead cutter With Safety Guard | 13.03 |
| 577—170LX | | J | Ergonomic, ESD safe shear cutter | 7.98 |
| 577—175LX | | K | Ergonomic, ESD safe shear cutter with safety guard | 10.75 |
| 577—175 | | J | Lead Cutter With Safety Guard | 7.99 |
| 577—1755 | | L | Wire/Cable Cutter | 16.44 |

Wira ESD SAFE PLIERS

- Cutting edges are induction hardened at a hardness of Approx. 64±HRC
- Two component non-slip soft grip handle
- ESD Safe Dissipative

For quantities of 6 and up, call for quote.

| MOUSER STOCK NO. | | Fig. | Description | Length | Price Each | |
|------------------|---------------|------|--|--------|------------|-------|
| Mfr. | Mfr. Part No. | | | | 1 | 5 |
| 596—32742 | | M | Pliers, Short Snipe Nose Straight, Serrated Jaws | 20mm | 40.54 | 29.38 |
| 596—32746 | | N | Pliers, Long Needle Nose, Straight, Serr. Jaws | 45mm | 46.18 | 33.49 |
| 596—32748 | | O | Pliers, Needle Nose, Bent 90°, Smooth Jaws | 45mm | 46.18 | 33.49 |
| 596—32750 | | P | Pliers, Short Round Nose, Smooth Jaws | 120mm | 40.54 | 29.38 |
| 596—32752 | | Q | Pliers, Short Flat Nose, Smooth Jaws | 120mm | 40.54 | 29.38 |