

TOSHIBA Transistors



This product is RoHS compliant.

TOSHIBA
Leading Innovation >>>



RoHS Compliant
For quantities of 2000 and up, call for quote.

TOSHIBA TRANSISTORS
Leading Innovation >>>

Transistors
Toshiba

MOUSER STOCK NO.	Toshiba Part No.	Package Type	Transistor Polarity	Voltage Output	Continuous Collector Current	Price Each				
						1	10	100	250	
Bias Resistor Built-in Transistors (cont.)										
757-RN2111FS(TPL3)	RN2111FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.066	.056	.051	
757-RN2111MFV(TPL3)	RN2111MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2112FS(TPL3)	RN2112FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.066	.056	.051	
757-RN2112MFV(TPL3)	RN2112MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2113FS(TPL3)	RN2113FS(TPL3)	fSM-3	PNP	20V	50 mA	.08	.066	.056	.051	
757-RN2113MFV(TPL3)	RN2113MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2114MFV(TPL3)	RN2114MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2115MFV(TPL3)	RN2115MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2116MFV(TPL3)	RN2116MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2117MFV(TPL3)	RN2117MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2118MFV(TPL3)	RN2118MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2119MFV(TPL3)	RN2119MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2130MFV(TPL3)	RN2130MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2131MFV(TPL3)	RN2131MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2132MFV(TPL3)	RN2132MFV(TPL3)	VESM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2301(TE85L,F)	RN2301(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2302(TE85L,F)	RN2302(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2303(TE85L,F)	RN2303(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2304(TE85L,F)	RN2304(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2305(TE85L,F)	RN2305(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2306(TE85L,F)	RN2306(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2307(TE85L,F)	RN2307(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2308(TE85L,F)	RN2308(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2309(TE85L,F)	RN2309(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2310(TE85L,F)	RN2310(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2311(TE85L,F)	RN2311(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2312(TE85L,F)	RN2312(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2313(TE85L,F)	RN2313(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2314(TE85L,F)	RN2314(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2315TE85LF	RN2315TE85LF	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2316(TE85L,F)	RN2316(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2317(TE85L,F)	RN2317(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2318(TE85L,F)	RN2318(TE85L,F)	USM-3	PNP	50V	100 mA	.06	.05	.043	.039	
757-RN2961FS(TPL3)	RN2961FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2962FS(TPL3)	RN2962FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2963FS(TPL3)	RN2963FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2964FS(TPL3)	RN2964FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2965FS(TPL3)	RN2965FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2966FS(TPL3)	RN2966FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2967FS(TPL3)	RN2967FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2968FS(TPL3)	RN2968FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2969FS(TPL3)	RN2969FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2970FS(TPL3)	RN2970FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2971FS(TPL3)	RN2971FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.084	.072	.066	
757-RN2972FS(TPL3)	RN2972FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN2973FS(TPL3)	RN2973FS(TPL3)	fS-6	PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4981(T5L,F,T)	RN4981(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4981FS(TPL3)	RN4981FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4982(T5L,F,T)	RN4982(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4982FS(TPL3)	RN4982FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.084	.072	.066	
757-RN4983(T5L,F,T)	RN4983(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4983FS(TPL3)	RN4983FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4984(T5L,F,T)	RN4984(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4984FS(TPL3)	RN4984FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.084	.072	.066	
757-RN4985(T5L,F,T)	RN4985(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4985FS(TPL3)	RN4985FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4986(T5L,F,T)	RN4986(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4986FS(TPL3)	RN4986FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.084	.072	.066	
757-RN4987FS(TPL3)	RN4987FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.084	.072	.066	
757-RN4988(T5L,F,T)	RN4988(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4988FS(TPL3)	RN4988FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4989(T5L,F,T)	RN4989(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4989FS(TPL3)	RN4989FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4990(T5L,F,T)	RN4990(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4990FS(TPL3)	RN4990FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4991(T5L,F,T)	RN4991(T5L,F,T)	US-6	NPN+PNP	50V	100 mA	.09	.07	.06	.055	
757-RN4991FS(TPL3)	RN4991FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4992FS(TPL3)	RN4992FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	
757-RN4993FS(TPL3)	RN4993FS(TPL3)	fS-6	NPN+PNP	20V	50 mA	.11	.085	.073	.066	

