

VECTRON RF Oscillators



This product is RoHS compliant.

VCC1 SERIES CMOS CRYSTAL OSCILLATORS 5 X 7 X 1.6MM

Features:

- CMOS output
- Output frequencies to 190MHz
- Low jitter, Fundamental or 3rd OT Crystal
- Tri-state output for board test and debug
- -10/70 or -40/85°C operating temperature
- Gold over nickel contact pads
- Hermetically sealed ceramic SMD package
- Product is compliant to RoHS directive and fully compatible with lead free assembly

Applications:

- SONET/SDH/DWDM
- Ethernet, Gigabit Ethernet
- Storage Area Network
- Digital Video
- Broadband Access
- Microprocessors/DSP/FPGA



RoHS Compliant

MOUSER STOCK NO.	Vectron Part No.	Voltage	Frequency (MHz)	Absolute Pull Range (ppm)	Price Each				Reel Quantity	Reel Price
					1	50	100	500		
711-VCC1-B3B-25M	VCC1-B3B-25M0000000	3.3	25.000	50	1.86	1.63	1.40	1.24	1000	1.12
711-VCC1-B3B-33M333	VCC1-B3B-33M3330000	3.3	33.333	50	1.86	1.63	1.40	1.24	1000	1.12
711-VCC1-B3B-50M	VCC1-B3B-50M0000000	3.3	50.000	50	1.86	1.63	1.40	1.24	1000	1.12
711-VCC1-B3B-66M667	VCC1-B3B-66M6670000	3.3	66.667	50	1.86	1.63	1.40	1.24	1000	1.12
711-VCC1-B3B-75M	VCC1-B3B-75M0000000	3.3	75.000	50	2.25	1.97	1.69	1.50	1000	1.35
711-VCC1-B3B-125M	VCC1-B3B-125M0000	3.3	125.000	50	3.45	3.02	2.59	2.30	1000	2.07
711-VCC1-B3B-100M	VCC1-B3B-100M000000	3.3	100.000	50	3.54	3.10	2.66	2.36	1000	2.12
711-VCC1-B3B-150M	VCC1-B3B-150M000000	3.3	150.000	50	5.40	4.73	4.05	3.60	1000	3.24
711-VCC1-B3D-25M	VCC1-B3D-25M0000000	3.3	25.000	50	2.34	2.05	1.76	1.56	1000	1.40
711-VCC1-B3D-33M333	VCC1-B3D-33M3330000	3.3	33.333	50	2.34	2.05	1.76	1.56	1000	1.40
711-VCC1-B3D-50M	VCC1-B3D-50M0000000	3.3	50.000	50	2.34	2.05	1.76	1.56	1000	1.40
711-VCC1-B3D-66M667	VCC1-B3D-66M6670000	3.3	66.667	50	2.34	2.05	1.76	1.56	1000	1.40
711-VCC1-B3D-75M	VCC1-B3D-75M0000000	3.3	75.000	50	2.85	2.49	2.14	1.90	1000	1.71
711-VCC1-B3D-100M	VCC1-B3D-100M000000	3.3	100.000	50	3.84	3.36	2.88	2.56	1000	2.30
711-VCC1-B3D-125M	VCC1-B3D-125M000000	3.3	125.000	50	4.35	3.81	3.26	2.90	1000	2.61
711-VCC1-FIBS-106M25	VCC1-FIBS-106M25	3.3	106.250	50	3.45	3.02	2.59	2.30	1000	2.07

VCC6-Q/R SERIES LVPECL CRYSTAL OSCILLATORS 5 X 7.5 X 2.2MM

Features:

- 2.5 or 3.3V LVPECL
- 3rd Overtone Crystal for best jitter performance
- Output frequencies to 270MHz
- 0.2pS rms jitter, 12kHz-20MHz, 155.52MHz
- Enable/Disable for test and board debug
- -10/70 or -40/85°C operating temperature
- Hermetically sealed ceramic SMD package
- Product is compliant to RoHS directive

Applications:

- SONET/SDH/DWDM
- Fiber Channel
- Ethernet, Gigabit Ethernet
- Storage Area Network
- Digital Video
- Broadband Access



RoHS Compliant

MOUSER STOCK NO.	Vectron Part No.	Supply Voltage (V)	Frequency (MHz)	Absolute Pull Range (ppm)	Price Each				Reel Quantity	Reel Price
					1	50	100	500		
711-VCC6-QCD-100M	VCC6-QCD-100M000000	3.3	100.00	50	18.54	16.22	13.91	12.36	1000	11.12
711-VCC6-QCD-125M	VCC6-QCD-125M000000	3.3	125.00	50	18.54	16.22	13.91	12.36	1000	11.12
711-VCC6-QCD-155M52	VCC6-QCD-155M520000	3.3	155.52	50	18.54	16.22	13.91	12.36	1000	11.12
711-VCC6-QCD-156M25	VCC6-QCD-156M250000	3.3	156.25	50	18.54	16.22	13.91	12.36	1000	11.12

VS-705 SERIES SINGLE FREQUENCY VCXO OSCILLATORS 5 X 7.5 X 2.5MM

Features:

- Industry Standard Package, 5.0 x 7.5 x 2.5mm
- 5th Generation ASIC Technology for Ultra Low Jitter
- 120 fs-rms (fN = 622.08MHz, 12kHz to 20MHz)
- 105 fs-rms (fN = 622.08MHz, 50kHz to 80MHz)
- Output Frequencies from 122.88MHz to 985.00MHz
- Spurious Suppression, 90dBc Typical
- 2.5V or 3.3V Supply Voltage
- LVPECL or LVDS Output Configurations
- Tri-State Output Select (OD, OS, OE)
- Compliant to EC RoHS Directive

C4400 Applications:

- 1-2-4 Gigabit Fibre Channel
- 10 Gigabit Fibre Channel
- 10GbE LAN / WAN
- Synchronous Ethernet
- OC-192
- SONET / SDH
- WiMax



RoHS Compliant

MOUSER STOCK NO.	Vectron Part No.	Output Type	Frequency (MHz)	Absolute Pull Range (ppm)	Price Each			Reel Quantity	Reel Price
					1	10	100		
711-705GAAN-155M52	VS-705-LFF-GAAN-155M520000	LVPECL	155.52000	50	62.88	55.02	47.16	250	41.92
711-705GAAN-320M	VS-705-LFF-GAAN-320M000000	LVPECL	320.00000	50	62.88	55.02	47.16	1000	33.54
711-705GAAN-491M52	VS-705-LFF-GAAN-491M520000	LVPECL	491.52000	50	62.88	55.02	47.16	1000	33.54
711-705GAAN-622M08	VS-705-LFF-GAAN-622M080000	LVPECL	622.08000	50	78.60	68.78	58.95	1000	41.92
711-705GAAN644M53125	VS-705-LFF-GAAN-644M531250	LVPECL	644.53125	50	78.60	68.78	58.95	200	52.40
711-705GAAN-800M	VS-705-LFF-GAAN-800M000000	LVPECL	800.00000	50	95.64	83.69	71.73	200	63.76
711-705GAAN-983M04	VS-705-LFF-GAAN-983M040000	LVPECL	983.04000	50	95.64	83.69	71.73	200	63.76
711-705HAAN-125M	VS-705-LFF-HAAN-125M000000	LVPECL	125.00000	100	67.29	58.88	50.47	250	44.86
711-705HAAN-156M25	VS-705-LFF-HAAN-156M250000	LVPECL	156.25000	100	67.29	58.88	50.47	250	44.86

NEW SUPPLIER

Frequency Control

Vectron

NEW SUPPLIER

NEW SUPPLIER

NEW SUPPLIER