


BK PRECISION PROGRAMMABLE DC ELECTRONIC LOADS



Features:

- CV/CC/CW/CR operation
- VFD display
- Over-current/Over-voltage/Over-temperature protected
- RS232 to TTL serial converter cable and application software included
- Optional USB interface available (order IT-E132)
- Thermostat controlled internal fan



MOUSER STOCK NO.	Fig.	Description	Price Each
615-8500	A	300 Watt, 120V, 30A	1050.00
615-8502	A	300 Watt, 500V, 15A	1150.00
615-8510	B	600 Watt, 120V, 120A	2050.00
615-8512	B	600 Watt, 500V, 30A	2495.00
615-8514	B	1200 Watt, 120V, 240	2950.00
615-8518	B	1200 Watt, 60V, 240A	3975.00
615-8520	C	2400 Watt, 120V, 240A	5350.00
615-8522	C	2400 Watt, 500V, 120A	6650.00
615-8524	D	5000 Watt, 60V, 240A	10150.00
615-8526	D	5000 Watt, 500V, 120A	12750.00
615-8540	E	150 Watt, 60V,30A, Non-Programmable	499.00

BK PRECISION DIGITAL STORAGE OSCILLOSCOPES

The B&K Precision Digital Storage Oscilloscopes deliver essential features and reliable performance at a price you can afford. Analog style knobs and controls combined with a smart Auto function make these oscilloscopes easy to use. Advanced triggering, automatic measurements and FFT functions provide you with many options to debug your circuits. Additionally, the instruments come with PC Software that lets you easily capture, analyze and document waveforms and measurement results. An ideal education and training tool and also well suited for applications in service and repair.



Features:

- Extensive Trigger capabilities including pulse width and line-selectable Video trigger
- 100 MHz bandwidth, 1GSa/s sample rate
- PC Software that lets you remotely control the oscilloscope and capture, save and analyze waveform data
- 4000 point record length for each channel

MOUSER STOCK NO.	BK Part No.	Description	Price Each
615-2542	2542	Color LCD, 100MHz, 1GSa/s	1155.00
615-2540	2540	Color LCD, 60MHz, 1GSa/s	940.00
615-2534	2534	Color LCD, 60MHz, 400MSa/s	799.00
615-2532	2532	One Touch Automatic, 64MHz, 500MSa/s	699.00
615-2530	2530	One Touch Automatic, 25MHz, 250MSa/s	496.31

BK PRECISION ANALOG OSCILLOSCOPES

30MHz

Specifications:

- 1 mV/div sensitivity X5 mag
- Dual or single trace operation
- Calibrated 19 step time base with x10 magnifier
- Compact low-profile design
- AUTO/NORM triggered sweep operation with AC, TVH, TVV, and line coupling

MOUSER STOCK NO.	BK Part No.	Description	Price Each
615-2120B	2120B	Dual Trace, 2 year warranty	599.00
615-2125A	2125A	Analog Oscilloscope, delayed sweep in 23 steps, 3 year warranty	646.00

100MHz

Specifications:

- Sweeps to 5ns/division
- 22 calibrated ranges, main time base
- Signal delay line
- 19 calibrated ranges on delayed time base
- Channel 1 output
- 15kV accelerating voltage
- Three year warranty

MOUSER STOCK NO.	BK Part No.	Description	Price Each
615-2190B	2190B	Dual-Trace Dual Time Base	1590.40

OSCILLOSCOPE ACCESSORIES

MOUSER STOCK NO.	BK Part No.	Description	Price Each
615-23701	PR-37AG	Probe gray	49.17
615-23702	PR-37AR	Probe red	50.00
615-PR-50	PR-50	3 Piece probe kit: probes x1, x100, and x1/x10 switchable. With sprung hook, replacement tip, ground lead and BNC adapter	110.00

BK PRECISION HANDHELD SPECTRUM ANALYZERS

- Channel power measurement
- Adjacent channel power measurement
- Occupied bandwidth measurement
- Electric field strength measurement (with optional dipole antennas)
- Magnetic field strength measurement (with optional PR 26M)
- Min/Max hold
- Average & over write mode
- Marker measurement
- Switchable 50Ω or 75Ω input impedance
- Peak search
- Auto tuning
- Auto range
- Save/Load
- Hard copy of display (with optional PT 2650)
- USB interface



615-2650A/52A



615-2658A

MOUSER STOCK NO.	BK Part No.	Frequency Range	Price Each
615-2650A	2650A	50KHz - 3.3 GHz	6450.00
615-2652A	2652A	50KHz - 3.3 GHz	8450.00
615-2658A	2658A	50KHz - 8.5 GHz with tracking generator	10395.00

BK PRECISION COUNTERS



615-1823A



615-1856D

2.4GHz Universal Counter

The model 1823 provides versatility and reliability for a broad spectrum of laboratory and service applications.

Specifications:

- Measures up to 2.4GHz
- Eight-digit display provides up to 0.1Hz resolution
- Period mode combines two input frequencies & displays their ratio
- Totalize mode and Time interval mode add versatility
- Selectable attenuators and low-pass filter prevent miscounts due to input point
- One year warranty
- Supplied: instruction manual

MOUSER STOCK NO.	BK Part No.	Price Each
615-1823A	1823A	460.00

3.5GHz Frequency Counter (Frequency, Period, Totalize)

The model 1856D provides versatility and reliability for a broad spectrum of laboratory and service applications.

Specifications:

- RS232 Interface
- Wide measuring range up to 3.5GHz
- Bright nine digit LED display
- Period mode for accurate low frequency measurement
- Totalize mode permits counting of individual events
- Accurate TCXO time base
- One Year Warranty
- Supplied: Instruction Manual

MOUSER STOCK NO.	BK Part No.	Price Each
615-1856D	1856D	527.15

BK PRECISION SIGNAL GENERATORS

Hand Held Battery Operated 10MHz Sine & Square Wave Generator

Features:

- 0.1Hz to 9.9999999MHz Sine/Square Wave Signal Generator
- Simultaneous Sine and Square wave generation
- 0.1Hz Frequency Selectability
- 0.02% Signal Accuracy
- Sine Wave Output - 0 to 4.5Vp-p (no load)
- Square Wave Output - 5Vp-p (no load)
- 50Ω output impedance



MOUSER STOCK NO.	BK Part No.	Price Each
615-3003	3003	210.00

Handheld NTSC Generator

This handheld NTSC Pattern Generator is powered by a 9 volt battery or AC adapter providing NTSC color bars, crosshatch, dot, staircase, circle, center cross, windows, and a full range of color raster patterns. The outputs available are composite video via RCA connector, a RF output BNC connector, or an S Video mini-DIN output. Signals can be produced as an interlaced or progressive scanning mode.

Features:

- S Video, composite video, RF output
- Interlace or progressive scanning system
- 9VDC battery (included)
- AC adapter available
- One year warranty



MOUSER STOCK NO.	BK Part No.	Price Each
615-1211E	1211E	250.00