


TRIQUINT SEMICONDUCTOR Evaluation Boards



This product is RoHS compliant.

WJ Communications, Inc. is a leading provider of (RF) solutions serving multiple markets targeting wireless communications, RF identification (RFID), broadband cable, defense, and homeland security. WJ addresses the RF challenges in these multiple markets with its highly reliable amplifiers, mixers, RF integrated circuits (RFICs), RFID reader modules, chipsets, and multi-chip (MCM) modules.



AP601-PCB1960

WJA1030-PCB

TQP3M9018/TQP3M9019

PRODUCT **NEW**

PRODUCT **NEW**

| MOUSER STOCK NO. | TriQuint Part No. | Description | Price Per Board | MOUSER STOCK NO. | TriQuint Part No. | Description | Price Per Board |
|-----------------------------|-------------------|---------------------------------|-----------------|-----------------------------|-------------------|------------------------------------|-----------------|
| 772-AG102-PCB | AG102-PCB | AG102 800-2600MHz Eval Brd | 66.67 | 772-TQP8M9013PCB2140 | TQP8M9013-PCB2140 | TQP8M9013 3.11-2.17GHz Eval Brd | 106.67 |
| 772-AG203-63PCB | AG203-63PCB | AG203-63 700-2400MHz Eval Brd | 66.67 | 772-TQP3M9008-PCB-RF | TQP3M9008-PCB-RF | TQP3M9008 0.5-4GHz Eval Brd | 66.67 |
| 772-AG302-63PCB | AG302-63PCB | AG302-63 700-2400MHz Eval Brd | 66.67 | 772-TQP3M9008-PCB-IF | TQP3M9008-PCB-IF | TQP3M9008 0.05-0.5GHz Eval Brd | 66.67 |
| 772-AG302-86PCB | AG302-86PCB | AG302-86 700-2400MHz Eval Brd | 66.67 | 772-TQP3M9009-PCB-RF | TQP3M9009-PCB-RF | TQP3M9009 0.5-4GHz Eval Brd | 66.67 |
| 772-AG303-63PCB | AG303-63PCB | AG303-63 700-2400MHz Eval Brd | 66.67 | 772-TQP3M9009-PCB-IF | TQP3M9009-PCB-IF | TQP3M9009 0.05-0.5GHz Eval Brd | 66.67 |
| 772-AG303-86PCB | AG303-86PCB | AG303-86 700-2400MHz Eval Brd | 66.67 | 772-TQP3M9018-PCB-RF | TQP3M9018-PCB-RF | TQP3M9018 .05-4GHz Eval Brd | 66.67 |
| 772-AG403-89PCB | AG403-89PCB | AG403-89 700-2400MHz Eval Brd | 66.67 | 772-TQP3M9019-PCB-RF | TQP3M9019-PCB-RF | TQP3M9019 .05-4GHz Eval Brd | 66.67 |
| 772-AG602-89PCB | AG602-89PCB | AG602-89 700-2400MHz Eval Brd | 66.67 | 772-TQP4M9072-PCB-IF | TQP4M9072-PCB_IF | TQP4M9072 40-500MHz Eval Brd | 106.67 |
| 772-AG604-86PCB | AG604-86PCB | AG604-86 700-2400MHz Eval Brd | 66.67 | 772-TQP4M9072-PCB-RF | TQP4M9072-PCB_RF | TQP4M9072 .7-3.5GHz Eval Brd | 106.67 |
| 772-AG604-89PCB | AG604-89PCB | AG604-89 700-2400MHz Eval Brd | 66.67 | 772-TQP4M9071-PCB-IF | TQP4M9071-PCB-IF | TQP4M9071 40MHz to 500MHz Eval Brd | 106.67 |
| 772-AH101-PCB | AH101-PCB | AH101 50-1500MHz Eval Brd | 133.33 | 772-TQP4M9071-PCB-RF | TQP4M9071-PCB-RF | TQP4M9071 .7GHz to 3.5GHz Eval Brd | 106.67 |
| 772-AH102A-PCB2000 | AH102A-PCB2000 | AH102A 1700-2200MHz Eval Brd | 133.33 | 772-AH3WB-PCB | AH3WB-PCB | AH3 50-870MHz Eval Brd | 106.67 |
| 772-AH102A-PCB900 | AH102A-PCB900 | AH102A 900MHz Eval Brd | 133.33 | 772-AH314-PCB | AH314-PCB | AH314 2.4-2.7GHz Eval Brd | 133.33 |
| 772-AH103A-PCB1900 | AH103A-PCB1900 | AH103A 1900MHz Eval Brd | 133.33 | 772-AH315-PCB | AH315-PCB | AH315 3.3-3.7GHz Eval Brd | 133.33 |
| 772-AH103A-PCB2140 | AH103A-PCB2140 | AH103A 2140MHz Eval Brd | 133.33 | 772-AP561-PCB2500 | AP561-PCB2500 | AP561 2.4-2.7GHz Eval Brd | 200.00 |
| 772-AH103A-PCB900 | AH103A-PCB900 | AH103A 900MHz Eval Brd | 133.33 | 772-AP601-PCB900 | AP601-PCB900 | AP601 869-960MHz Eval Brd | 200.00 |
| 772-AH114-89PCB1900 | AH114-89PCB1900 | AH114 1900MHz Eval Brd | 106.67 | 772-AP601-PCB1960 | AP601-PCB1960 | AP601 1930-1990MHz Eval Brd | 200.00 |
| 772-AH114-89PCB2140 | AH114-89PCB2140 | AH114 2140MHz Eval Brd | 106.67 | 772-AP601-PCB2140 | AP601-PCB2140 | AP601 2110-2170MHz Eval Brd | 200.00 |
| 772-AH114-89PCB900 | AH114-89PCB900 | AH114 900MHz Eval Brd | 106.67 | 772-AP602-PCB900 | AP602-PCB900 | AP602 869-960MHz Eval Brd | 200.00 |
| 772-AH118-89PCB2140 | AH118-89PCB2140 | AH118 2140MHz Eval Brd | 106.67 | 772-AP602-PCB1960 | AP602-PCB1960 | AP602 1930-1990MHz Eval Brd | 200.00 |
| 772-AH118-89PCB900 | AH118-89PCB900 | AH118 900MHz Eval Brd | 106.67 | 772-AP602-PCB2140 | AP602-PCB2140 | AP602 2110-2170MHz Eval Brd | 200.00 |
| 772-AH11PP1900-PCB | AH11PP1900-PCB | AH11 1900MHz Push-Pull Eval Brd | 106.67 | 772-AP603-PCB900 | AP603-PCB900 | AP603 869-960MHz Eval Brd | 200.00 |
| 772-AH11PP900-PCB | AH11PP900-PCB | AH11 900MHz Push-Pull Eval Brd | 106.67 | 772-AP603-PCB1960 | AP603-PCB1960 | AP603 1930-1990MHz Eval Brd | 200.00 |
| 772-AH1-PCB | AH1-PCB | AH1 800-2500MHz Eval Brd | 106.67 | 772-AP603-PCB2140 | AP603-PCB2140 | AP603 2110-2170MHz Eval Brd | 200.00 |
| 772-AH202-PCB1900 | AH202-PCB1900 | AH202 1900 MHz Eval Brd | 200.00 | 772-EC1078B-PCB | EC1078B-PCB | EC1078B-PCB | 106.67 |
| 772-AH202-PCB2140 | AH202-PCB2140 | AH202 2140 MHz Eval Brd | 200.00 | 772-ECG001B-PCB | ECG001B-PCB | ECG001B 700-2400MHz Eval Brd | 66.67 |
| 772-AH202-PCB900 | AH202-PCB900 | AH202 900 MHz Eval Brd | 200.00 | 772-ECG001F-PCB | ECG001F-PCB | ECG001F 700-2400MHz Eval Brd | 66.67 |
| 772-AH212-S8PCB1960 | AH212-S8PCB1960 | AH212-S8 1960MHz Eval Brd | 133.33 | 772-ECG003B-PCB | ECG003B-PCB | ECG003B 700-2400MHz Eval Brd | 66.67 |
| 772-AH212-S8PCB2140 | AH212-S8PCB2140 | AH212-S8 2140MHz Eval Brd | 133.33 | 772-ECG004B-PCB | ECG004B-PCB | ECG004B 700-2400MHz Eval Brd | 66.67 |
| 772-AH215-S8PCB1960 | AH215-S8PCB1960 | AH215 1960MHz Eval Brd | 133.33 | 772-ECG005B-PCB | ECG005B-PCB | ECG005B 700-2400MHz Eval Brd | 66.67 |
| 772-AH215-S8PCB2140 | AH215-S8PCB2140 | AH215 2140MHz Eval Brd | 133.33 | 772-ECG006C-PCB | ECG006C-PCB | ECG006C 700-2400MHz Eval Brd | 66.67 |
| 772-AH215-S8PCB900 | AH215-S8PCB900 | AH215 900MHz Eval Brd | 133.33 | 772-ECG006F-PCB | ECG006F-PCB | ECG006F 700-2400MHz Eval Brd | 66.67 |
| 772-AH22S-PCB | AH22S-PCB | AH22S CATV Push-Pull Eval Brd | 106.67 | 772-ECG008B-PCB | ECG008B-PCB | ECG008B 700-2400MHz Eval Brd | 66.67 |
| 772-AH2-PCB | AH2-PCB | AH2 50-860MHz CATV Eval Brd | 106.67 | 772-ECG055B-PCB | ECG055B-PCB | ECG055B 700-2400MHz Eval Brd | 66.67 |
| 772-AH312-S8PCB1960 | AH312-S8PCB1960 | AH312 1960MHz Eval Brd | 200.00 | 772-FP1189-PCB1900S | FP1189-PCB1900S | FP1189 1900MHz Eval Brd | 106.67 |
| 772-AH312-S8PCB2140 | AH312-S8PCB2140 | AH312 2140MHz Eval Brd | 200.00 | 772-FP1189-PCB2140S | FP1189-PCB2140S | FP1189 2140MHz Eval Brd | 106.67 |
| 772-AH312-S8PCB900 | AH312-S8PCB900 | AH312 900MHz Eval Brd | 200.00 | 772-FP1189-PCB900S | FP1189-PCB900S | FP1189 900MHz Eval Brd | 106.67 |
| 772-AH31-PCB170 | AH31-PCB170 | AH31 155-185MHz Eval Brd | 106.67 | 772-FP2189-PCB1900S | FP2189-PCB1900S | FP2189 1900MHz Eval Brd | 133.33 |
| 772-AH31-PCB240 | AH31-PCB240 | AH31 220-260MHz Eval Brd | 106.67 | 772-FP2189-PCB2140S | FP2189-PCB2140S | FP2189 2140MHz Eval Brd | 133.33 |
| 772-AH31-PCB500 | AH31-PCB500 | AH31 450-550MHz Eval Brd | 106.67 | 772-FP2189-PCB900S | FP2189-PCB900S | FP2189 900MHz Eval Brd | 133.33 |
| 772-AH31-PCB75 | AH31-PCB75 | AH31 65-85MHz Eval Brd | 106.67 | 772-FP31QF-PCB1900 | FP31QF-PCB1900 | FP31QF 1900MHz Eval Brd | 200.00 |
| 772-ML483-PCB | ML483-PCB | ML483 .7GHz to 1GHz Eval Bd | 66.67 | 772-FP31QF-PCB2140 | FP31QF-PCB2140 | FP31QF 2140MHz Eval Brd | 200.00 |
| 772-TQM8M9074-EVAL | TQM8M9074-Eval | TQM8M9074 2140MHz Eval Brd | 106.67 | 772-FP31QF-PCB900 | FP31QF-PCB900 | FP31QF 900MHz Eval Brd | 200.00 |
| 772-TQP3M9006EV | TQP3M9006-PCB | TQP3M9006 0.5-4GHz Eval Brd | 66.67 | 772-WJA1010-PCB | WJA1010-PCB | WJA1010 50-2300MHz Eval Brd | 66.67 |
| 772-TQP3M9007-PCB | TQP3M9007-PCB | TQP3M9007 0.5-4GHz Eval Brd | 66.67 | 772-WJA1015-PCB | WJA1015-PCB | WJA1015 50-2300MHz Eval Brd | 66.67 |
| 772-TQP3M9028-PCB-RF | TQP3M9028-PCB-RF | TQP3M9028 0.5-4GHz Eval Brd | 66.67 | 772-WJA1030-PCB | WJA1030-PCB | WJA1030 50-4000MHz Eval Brd | 66.67 |
| 772-TQP7M9101PCB2140 | TQP7M9101-PCB2140 | TQP7M9101 2.11-2.17GHz Eval Brd | 106.67 | 772-WJA1500-PCB | WJA1500-PCB | WJA1500 50-1000MHz Eval Brd | 66.67 |
| 772-TQP7M9101-PCB900 | TQP7M9101-PCB900 | TQP7M9101 869-960MHz Eval Brd | 106.67 | 772-WJA1505-PCB | WJA1505-PCB | WJA1505 50-1000MHz Eval Brd | 66.67 |
| 772-TQP7M9102PCB2140 | TQP7M9102-PCB2140 | TQP7M9102 2.11-2.17GHz Eval Brd | 106.67 | 772-WJA1510-PCB | WJA1510-PCB | WJA1510 50-1000MHz Eval Brd | 66.67 |
| 772-TQP7M9102-PCB900 | TQP7M9102-PCB900 | TQP7M9102 869-960MHz Eval Brd | 106.67 | 772-WJA1515-PCB | WJA1515-PCB | WJA1515 50-1000MHz Eval Brd | 66.67 |
| 772-TQP8M9013PCB900 | TQP8M9013-PCB900 | TQP8M9013 850-900MHz Eval Brd | 106.67 | | | | |