


Pure Lead and Sealed Lead Acid Batteries



EnerSys PURE LEAD RECHARGEABLE BATTERIES

- High-Rate Power Density
- Capable of more than 300 Cycles
- High Stable Voltage Delivery
- Wide Temperature Range:
Cyclon Single Cells: -65°C ~ +80°C
Monobloc: -40°C ~ +40°C
- Fast Recharge: up to 95% Recharge in Less Than One Hour
- Maintains Performance and Physical Parameters in Extreme Conditions
- Can be mounted and operated in any position
- Provides the Longest Service Life Possible
- Low Self-Discharge Rate
- Rugged Construction

Cyclon 2 Volt Single Cells

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	EnerSys Part No.	Fig.	Size	Capacity (Ah)	Dimensions: in.					Price Each			
					Diameter	Height	Height Over Term.	Weight (lbs.)	Tabs	1	5	10	25
846-0810-0004	0810-0004	A	D	2.5	1.35	2.41	2.68	0.39	.187 x 0.25	10.84	9.94	9.40	8.99
846-0800-0004	0800-0004	A	X	5.0	1.75	2.87	3.21	0.80	.250 x .025	15.08	13.86	13.04	12.63


Cyclon 4 and 6 Volt Monoblocs

For quantities of 50 and up, call for quote.

MOUSER STOCK NO.	EnerSys Part No.	Fig.	Size	Capacity (Ah)	Dimensions: in.					Price Each			
					Diameter	Height	Height Over Term.	Weight (lbs.)	Tabs	1	5	10	25
4 Volt													
846-0819-0010	0819-0010	B	D	2.5	3.13	1.81	2.75	0.8	0.187 x .025	22.10	20.32	19.12	17.93
846-0809-0010	0809-0010	B	X	5.0	3.80	2.12	3.02	1.62	0.250 x .025	28.77	26.44	24.88	23.33
846-0859-0010	0859-0010	B	E	8.0	3.81	2.13	4.00	2.11	0.250 x .025	24.55	22.88	22.57	22.11
6 Volt													
846-0819-0012	0819-0012	C	D	2.5	4.48	1.81	2.75	1.15	0.187 x .025	26.73	24.57	23.12	21.68
846-0809-0012	0809-0012	C	X	5.0	5.48	2.12	3.02	2.16	0.250 x .025	32.65	31.77	30.01	28.24
846-0859-0012	0859-0012	C	E	8.0	5.48	2.13	4.00	3.15	0.250 x .025	41.73	38.24	36.05	33.65

POWERED BY Panasonic BATTERIES SEALED LEAD-ACID BATTERIES

- High Quality and Reliability
- Exceptional Deep Discharge Recover
- No Corrosive Gas Generation
- Long Service Life
- Quick Chargeability
- High Power Density
- Maintenance-Free Operation



For quantities of 10 and up, call for quote.

MOUSER STOCK NO.	Panasonic Part No.	Nominal Voltage	Capacity 20 Hr. Rate (Ah)	Terminal Type	Dimensions: in.			Weight (lbs.)	Cycle Use		Trickle Use		Price Each
					L	W	H		Initial Current	Control Volt.	Initial Current	Control Volt.	
658-LC-R063R4P	LC-R063R4P	6	3.4	.187" Faston	5.28	1.34	2.36	1.37	1.36A	14.5-14.9V	0.51A	13.6-13.8V	26.75
658-LCR064R5P	LC-R064R5P	6	4.5	.187" Faston	2.76	1.89	4.02	1.59	1.80A	7.25-7.45V	.675A	6.8-6.9V	15.84
658-LCR067R2P	LC-R067R2P	6	7.2	.187" Faston	5.95	1.34	3.70	2.78	2.88A	7.25-7.45V	1.08A	6.8-6.9V	26.20
658-LCR067R2P1	LC-R067R2P1	6	7.2	.250" Faston	5.95	1.34	3.70	2.78	2.88A	7.25-7.45V	1.08A	6.8-6.9V	26.20
658-LCR0612P	LC-R0612P	6	12.0	.187" Faston	5.95	1.97	3.70	4.30	4.8A	7.25-7.45V	1.8A	6.8-6.9V	36.09
658-LCR0612P1	LC-R0612P1	6	12.0	.250" Faston	5.95	1.97	3.70	4.30	4.8A	7.25-7.45V	1.8A	6.8-6.9V	45.46
658-LC-R121R3P	LC-R121R3P	12	1.3	.187" Faston	3.82	1.87	1.97	1.30	4.8A	7.25-7.45V	1.8A	6.8-6.9V	28.28
658-LC-R122R2P	LC-R122R2P	12	2.2	.187" Faston	6.97	1.34	2.36	1.76	0.88A	14.5-14.9V	0.33A	13.6-13.8V	33.13
658-LC-R123R4P	LC-R123R4P	12	3.4	.187" Faston	5.28	2.64	2.36	2.65	1.36A	14.5-14.9V	0.51A	13.6-13.8V	39.49
658-LCR127R2P	LC-R127R2P	12	7.2	.187" Faston	5.95	2.54	3.70	5.45	2.88A	14.5-14.9V	1.08A	13.6-13.8V	39.26
658-LCR127R2P1	LC-R127R2P1	12	7.2	.250" Faston	5.95	2.54	3.70	5.45	2.88A	14.5-14.9V	1.08A	13.6-13.8V	39.26
658-LCRD1217P	LC-RD1217P	12	17.0	Nut and Bolt	7.13	2.99	6.57	14.34	6.8A	14.5-14.9V	2.55A	13.6-13.8V	93.35
658-LCLA1233P	LC-LA1233P	12	33.0	Nut and Bolt	7.70	5.12	6.10	26.50	13.2A	14.5-14.9V	4.95A	13.6-13.8V	175.93

BK PRECISION BATTERY CAPACITY ANALYZER

Applications:
The need for battery maintenance tools is growing for use in Automotive, Field Service and Maintenance, Telecommunications, and UPS Manufacturing/Maintenance applications. Perfect instrument for anyone working with UPS systems, Emergency back-up Flood Lights, Home and Business Security Alarm Systems, or for any applications using a 12 volt lead acid battery.

- Specifications:**
- Measures both No Load Voltage and Battery Capacity
 - Displays storage capacity of 12V lead acid batteries as a percentage
 - Powered by battery under test

For quantities of 5 and up, call for quote.

MOUSER STOCK NO.	B & K Part No.	Max Input Volt	Dimensions: in.			Weight (lbs)	Cap. Display Range	Price Each
			W	H	D			
615-600	600	20V	3.14	6.30	1.60	2.20	0-100%	315.56
615-601	601	20V	3.14	9.50	1.60	2.30	0-100%	419.00



Rechargeable