





ROHS COMPLIANT









MATERIAL:

BODY:

CONTACT:

INSULATOR:

FINISH:

BODY & CONTACT:

PERFORMANCE:

IMPEDANCE:

FREQ. RANGE:

INSUL. RES.:

STAINLESS STEEL PER AMS-5640,
ALLOY No. UNS S30300, TYPE 1

BERYLLIUM COPPER PER ASTM B196,
ALLOY No. UNS C17300, TD04


PTFE PER ASTM D1710, TYPE I, GRADE 1, CLASS B

GOLD PER ASTM B488, TYPE II, CODE C
CLASS 1.27 OVER NICKEL PER AMS-QQ-N-290

50 OHMS
DC TO 18.0 GHz
5000 MEGOHMS, MIN.

NOTES:

1. FOR RECOMMENDED FOOTPRINT TO YOUR SPECIFIC PCB,
CONTACT SV MICROWAVE SALES DEPARTMENT
(sales@svmicro.com, 561-840-1800).

MATERIAL:	SEE NOTES	DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: X ±.030 XX ±.010 XXX ±.005 INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994	UNLESS OTHERWISE SPECIFIED 1) ALL DIMENSIONS ARE IN INCHES (MILLIMETERS) 2) ALL DIMENSIONS ARE AFTER PLATING. 3) BREAK CORNERS & EDGES .005 R. MAX. 4) CHAM. 1ST & LAST THREADS. 5) SURFACE ROUGHNESS 63-MIL-STD-10. 6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN .005 T.I.R. 7) REMOVE ALL BURRS	2400 Centrepark West Drive, Suite 100 West Palm Beach, FL 33409	
FINISH:	SEE NOTES				
SURFACE AREA:	N/A				
THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.		THIRD ANGLE PROJECTION	DRAWN: JMC 03/10/10	TITLE: SMP MALE PCB EDGE MOUNT	
			CHECKED: PJS 03/10/10		
			APPROVED: PJS 03/10/10	SCALE: 16:1	SHEET 1 OF 1