

Antenna - ANT-OMNI-5900-01 - 2701347

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Omnidirectional antenna, 5 GHz, 5 dBi gain, linear vertical polarization, apex angle h/v 360°/25°, N (female), IP 64



Product Features

- ✓ For mobile or point-to-multipoint applications with a larger range

Key commercial data

Packing unit	0
Minimum order quantity	1
GTIN	 4 046356 739399
Custom tariff number	85177011
Country of origin	GERMANY

Technical data

General data

Frequency range	5 GHz
Frequency range	5.15 GHz ... 5.875 GHz
Horizontal beamwidth	360 °
Vertical beamwidth	25 °
Impedance	50 Ω
Gain	5 dBi
Connection method	N (female)
Degree of protection	IP64
Ambient temperature (operation)	-45 °C ... 70 °C
Ambient temperature (storage/transport)	-45 °C ... 70 °C
Width	16 mm
Height	130 mm

Classifications

ETIM

ETIM 3.0	EC001423
----------	----------

Antenna - ANT-OMNI-5900-01 - 2701347

Classifications

ETIM

ETIM 4.0	EC000416
ETIM 5.0	EC000416

UNSPSC

UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	20142601
UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215
eCl@ss 5.1	27242208
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208