




This drawing is the property of Tusonix, Inc., and may not be used, reproduced, published or disclosed to others without expressed authorization by Tusonix Inc.

Electrical Testing per Tusonix standard test plans and Mil-Std-202 Test Methods.

MARKETING SALES DRAWING
DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING
DIMENSIONS IN METRIC - []



- NOTES:**
1. TUSONIX STANDARD PART NUMBER: 513-010 A 1.0-5. TUSONIX RoHS COMPLIANT PART NUMBER: 513-010 A 1.0-5 LF. CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
 2. TERMINALS AND ROTOR ARE COPPER ALLOY RoHS COMPLIANT MATERIALS WITH SILVER PLATING.
 3. PART MARKING: TUSONIX TRADEMARK, CAPACITANCE RANGE AND DIELECTRIC TYPE CODE: STANDARD PART: BLACK INK. RoHS PART: DARK GREEN INK.
 4. DIMENSION TOLERANCES
 $\leq .125" [3.18] = \pm .005 [0.13]$
 $\geq .126" [3.20] = \pm .015 [0.38].$

SPECIFICATIONS	
Tusonix Style.	513 - 010
Value:	1.0 - 5pF
Value Tol.:	MIN. +10%, MAX. -10% +100%
Rating:	100 VDC
Diel. Code:	A (NP0)
Operating Range:	-55°C TO + 85°C
To Tusonix Spec Unless Stated Otherwise	

X-2015 Rev-0 REVISION RECORD Original Release C.O. ECO-785	A	TOLERANCES unless otherwise specified 2 PLC. DECIMAL ± // 3 PLC. DECIMAL ± // ANGLES ± //	Title LOW PROFILE CERAMIC TRIMMER	
			Drawn L.E. 06-04-09	Scale 5 X
			Approved R.L. 06-04-09	
		A	513-010 A 1.0-5	

TUSONIX
TUCSON, ARIZONA