




Dimensions (In.)

Specifications:

- Type: PC mount
- Primary voltage: 115VAC 60Hz
- Primary exciting current: 20mA (max.)
- Secondary voltage (no load): 14.6CT VAC $\pm$ 0.5V
- Secondary voltage (full load): 12.6CT VAC $\pm$ 0.5V
- Rated secondary current: 0.06A (AC) @ 60Hz
- Voltage regulation: $<16\% (V_{NL} - V_{FL}) / (V_{FL}) \times 100$
- Temperature rise: $<45^{\circ}\text{C}$
- Breakdown voltage (hi-pot): 2000VAC @ 50Hz for 1 minute
- Coil to coil insulation: 200M Ω (min.) 500VDC
- Strain relief: 5 lbs
- Channel frame material: 0.5mm thick iron
- Crossover insulation: 0.05mm thick polyester tape
- Core material and size: hilite core 0.5mm thick H-23, EI-28
- Inner insulation: 3 layers of 0.05mm thick polyester tape
- Outer wrap insulation: 3 layers of 0.05mm thick yellow polyester tape with 1 piece of fiber board
- Bobbin: nylon, type no. 66 normal 8mm x 11.2mm
- Impregnation: varnish
- Lead wire: AWG23~AWG25
- Lead length: .591" $\pm$.197"