








Dimensions (In.) (except where noted)

Specifications:

- Switch circuit: P/P DPDT
- Taper: linear
- Rated voltage: 200V
- Rated wattage: 0.2W
- Rotation angle: 300° ±5°
- Rotation torque: 20~200 gf.cm
- Rotation life: 15,000 cycles
- Insulation resistance: >100MΩ @ 500VDC
- Switch contact resistance: <20mΩ
- Usable temperature range: -10°C~70°C
- Dielectric: 500VAC for 1 minute
- Breakdown voltage: 500VAC for 1 minute
- Tolerance: <1M: ±20%, ≥1M: ±30%
- Switch rating: 0.3A, 30VDC
- Shaft stop strength: 6Kg.cm static load/min.
- Switch working angle (stroke): 4mm
- Switch working torque (force): 800gf.cm (max.)
- Switch life: 10,000 times
- Terminals: PC pins
- Values: 1K, 5K, 10K, 50K, & 100K
- Each supplied with 1 hex nut & 1 flat washer