

4

3




2

1

used for:

D-SUB

POS.	A -0.76	B -0.25	C	Art.-NO.
9	31.19	16.46	25.00 $+0.12$ -0.13	302A10019X
15	39.52	24.79	33.30 $+0.15$ -0.1	302A10029X
25	53.42	38.50	47.04 ± 0.13	302A10059X
37	69.70	54.96	63.50 ± 0.13	302A10069X



NOTES:

1. METALSHELLS: STEEL; min. 320µ" TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
4. PLATING: min. 8µ" HARD GOLD OVER min. 50µ" NICKEL
5. ACCEPTS CABLE AWG 20
6. = CRITICAL DIMENSION: SPC

Directive 2002/95/EC
„RoHS“
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.

DO NOT ALTER CAD DRAWING BY HAND

				tolerance		
				2001	date	name
				drawn	28.05.	Parei
				appd.	28.05.	E. Mickenbecker
				norm	DIN 41652	
				d-old		
						
rev.	description	date	name			

scale:	2:1	
material:	SEE NOTES	
title:	D-SUB FEMALE 9-37pos. SOLDER CUP STAMPED CONTACTS	
dwg no:	AutoCAD 2000	DIN-A
	16K1A206A	4
part no:	SEE TABLE	
		sh:1/2

4

3

2

1