


Vishay High Power Products

Schottky Rectifier, 30 A


IQR



PRODUCT SUMMARY				
I _{F(AV)} 30 A				
V _R	35 to 45 V			

FEATURES

- 150 °C T_J operation
- · Center tap TO-220 package
- · Low forward voltage drop
- · High frequency operation



- Guard ring for enhanced ruggedness and long term reliability
- Lead (Pb)-free ("PbF" suffix)
- Designed and qualified for industrial level

DESCRIPTION

The 25CTQ...PbF center tap Schottky rectifier series has been optimized for very low forward voltage drop, with moderate leakage. The proprietary barrier technology allows for reliable operation up to 150 °C junction temperature. Typical applications are in switching power supplies, converters, freewheeling diodes, and reverse battery protection.

MAJOR RATINGS AND CHARACTERISTICS					
SYMBOL	CHARACTERISTICS	VALUES	UNITS		
I _{F(AV)}	Rectangular waveform	30	А		
V _{RRM}	Range	35 to 45	V		
I _{FSM}	t _p = 5 μs sine	p = 5 μs sine 990			
V _F	15 Apk, T _J = 125 °C (per leg)	15 Apk, T _J = 125 °C (per leg) 0.50			
T _J	Range	Range - 55 to 150			

VOLTAGE RATINGS					
PARAMETER	SYMBOL	25CTQ035PbF	25CTQ040PbF	25CTQ045PbF	UNITS
Maximum DC reverse voltage	V_R	35	40	45	V
Maximum working peak reverse voltage	V_{RWM}	35			

ABSOLUTE MAXIMUM RATINGS					
PARAMETER	SYMBOL	TEST CONDITIONS VAL		VALUES	UNITS
Maximum average forward current See fig. 5	I _{F(AV)}	50 % duty cycle at T _C = 102 °C, rectangular waveform 30		Α	
Maximum peak one cycle non-repetitive surge current per leg		5 µs sine or 3 µs rect. pulse	Following any rated load condition and with rated	990	Α
See fig. 7	I _{FSM}	10 ms sine or 6 ms rect. pulse	V _{RRM} applied	250	ζ
Non-repetitive avalanche energy per leg	E _{AS}	$T_J = 25 ^{\circ}\text{C}, I_{AS} = 3.0 \text{A}, L = 4.40 \text{mH}$		mJ	
Repetitive avalanche current per leg	I _{AR}	Current decaying linearly to zero in 1 μ s Frequency limited by T_J maximum $V_A = 1.5 \text{ x } V_R$ typical		А	

^{*} Pb containing terminations are not RoHS compliant, exemptions may apply

25CTQ...PbF Series

Vishay High Power Products Schottky Rectifier, 30 A



ELECTRICAL SPECIFICATIONS						
PARAMETER	SYMBOL	L TEST CONDITIONS VALUES		UNITS		
	V _{FM} ⁽¹⁾	15 A	- T _J = 25 °C	0.56	V	
Maximum forward voltage drop per leg		30 A		0.71		
See fig. 1		15 A	T _J = 125 °C	0.50		
		30 A		0.64		
Maximum reverse leakage current per leg	I _{RM} ⁽¹⁾	T _J = 25 °C	$V_{\rm B}$ = Rated $V_{\rm B}$	1.75	mA	
See fig. 2	'RM \''	T _J = 125 °C	V _R = nateu V _R	70	IIIA	
Maximum junction capacitance per leg	C _T	V _R = 5 V _{DC} (test signal range 100 kHz to 1 MHz) 25 °C		900	pF	
Typical series inductance per leg	L _S	Measured lead to lead 5 mm from package body 8.0		8.0	nH	
Maximum voltage rate of change	dV/dt	Rated V _R 10 000			V/µs	

Note

 $^{^{(1)}\,}$ Pulse width < 300 $\mu s,$ duty cycle < 2 %

THERMAL - MECHANICAL SPECIFICATIONS					
PARAMETER		SYMBOL	TEST CONDITIONS	VALUES	UNITS
Maximum junction and storage temperature range		T _J , T _{Stg}		- 55 to 150	°C
Maximum thermal resistance, junction to case per leg		D	DC operation See fig. 4	3.25	
Maximum thermal resistance, junction to case per package		R_{thJC}	DC operation	1.63	°C/W
Typical thermal resistance, case to heatsink		R _{thCS}	Mounting surface, smooth and greased	0.50	
Approximate weight				2.0	g
Approximate weight				0.07	OZ.
	minimum			6 (5)	kgf · cm
Mounting torque	maximum			12 (10)	(lbf · in)
Marking device				25CTQ045	



Schottky Rectifier, 30 A

Vishay High Power Products




Fig. 1 - Maximum Forward Voltage Drop Characteristics (Per Leg)




Fig. 2 - Typical Values of Reverse Current vs. Reverse Voltage (Per Leg)




Fig. 3 - Typical Junction Capacitance vs. Reverse Voltage (Per Leg)




Fig. 4 - Maximum Thermal Impedance Z_{thJC} Characteristics (Per Leg)

Vishay High Power Products Schottky Rectifier, 30 A






Fig. 5 - Maximum Allowable Case Temperature vs. Average Forward Current (Per Leg)




Fig. 6 - Forward Power Loss Characteristics (Per Leg)




Fig. 7 - Maximum Non-Repetitive Surge Current (Per Leg)




Fig. 8 - Unclamped Inductive Test Circuit




Schottky Rectifier, 30 A

Vishay High Power Products

ORDERING INFORMATION TABLE

Device code



1 - Current rating (25 = 25 A)

2 - Circuit configuration

C = Common cathode

3 - Package

T = TO-220

4 - Schottky "Q" series

035 = 35 V 040 = 40 V

5 - Voltage ratings

040 = 40 V 045 = 45 V

6 - None = Standard production

• PbF = Lead (Pb)-free

Tube standard pack quantity: 50 pieces

LINKS TO RELATED DOCUMENTS				
Dimensions http://www.vishay.com/doc?95222				
Part marking information	http://www.vishay.com/doc?95215			



Vishay

Notice

The products described herein were acquired by Vishay Intertechnology, Inc., as part of its acquisition of International Rectifier's Power Control Systems (PCS) business, which closed in April 2007. Specifications of the products displayed herein are pending review by Vishay and are subject to the terms and conditions shown below.

Specifications of the products displayed herein are subject to change without notice. Vishay Intertechnology, Inc., or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document. Except as provided in Vishay's terms and conditions of sale for such products, Vishay assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of Vishay products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Vishay for any damages resulting from such improper use or sale.

International Rectifier®, IR®, the IR logo, HEXFET®, HEXSense®, HEXDIP®, DOL®, INTERO®, and POWIRTRAIN® are registered trademarks of International Rectifier Corporation in the U.S. and other countries. All other product names noted herein may be trademarks of their respective owners.

Document Number: 99901 www.vishay.com
Revision: 12-Mar-07 1