



Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207
Tel: 1-800-52 ALPHA (25742), Web: www.alphawire.com

Customer Specification

PART NO. 6360

Construction

			Diameters (In)				
1) Component 1	25 X 1 COND						
a) Conductor	24 (7/32) AWG TC			0.024			
b) Insulation	0.016" Wall, Nom. Polyethylene, Foam			0.056			
(1) Color Code	Alpha Wire Color Code F						
Cond	Color	Cond	Color	Cond	Color		
1	BLACK	10	ORANGE/BLACK	19	BLUE/RED		
2	WHITE	11	BLUE/BLACK	20	RED/GREEN		
3	RED	12	BLACK/WHITE	21	ORANGE/GREEN		
4	GREEN	13	RED/WHITE	22	BLACK/WHITE/RED		
5	ORANGE	14	GREEN/WHITE	23	WHITE/BLACK/RED		
6	BLUE	15	BLUE/WHITE	24	RED/BLACK/WHITE		
7	WHITE/BLACK	16	BLACK/RED	25	GREEN/BLACK/WHITE		
8	RED/BLACK	17	WHITE/RED				
9	GREEN/BLACK	18	ORANGE/RED				
2) Cable Assembly	25 Components Cabled						
a) Twists:	2.4 Twists/foot (min)						
3) Shield:	Alum/Mylar Tape, 25% Overlap, Min.						
a) Foil Direction	Foil Facing Out						
b) Drain Wire	24 (7/32) AWG TC						
c) Braid	TC, 65% Coverage, Min.						
4) Jacket	0.035" Wall, Nom., PVC			0.432 (0.452 Max.)			
a) Color(s)	SLATE						
b) Print	ALPHA WIRE-* P/N 6360 25C 24 AWG SHIELDED 75C (UL) TYPE CM OR AWM 2919 LOW VOLTAGE COMPUTER CABLE --- LLXXXXXX CSA TYPE CMH FT1 ROHS * = Factory Code [Note: Product may have c(UL) or CSA markings depending upon plant of manufacture.]						

Applicable Specifications

1) UL	AWM/STYLE 2919	80°C / 30 V _{RMS}
	CM	75°C
	VW-1	
2) CSA International	CMH	60°C
	FT1	

Environmental

1) EU Directive 2002/95/EC(RoHS):

All materials used in the manufacture of this part are in compliance with EU Directive 2002/95/EU regarding the restriction of use of certain hazardous substances in electrical and electronic equipment. Consult Alpha Wire's web site for compliance Date of Manufacture.

2) California Proposition 65:

The outer surface materials used in the manufacture of this part meet the requirements of California Proposition 65.

Properties

Physical & Mechanical Properties

1) Temperature Range	-20 to 80°C
2) Bend Radius	10X Cable Diameter
3) Pull Tension	98 Lbs, Maximum
Electrical Properties	(For Engineering purposes only)
1) Voltage Rating	300 V _{RMS}
2) Mutual Capacitance	12 pf/ft @1 kHz, Nominal
3) Ground Capacitance	22 pf/ft @1 kHz, Nominal
4) Conductor DCR	26 /1000ft @20°C, Nominal
5) OA Shield DCR	2.6 /1000ft @20°C, Nominal

Other

Packaging	Flange x Traverse x Barrel (inches)
a) 1000 FT	24 x 14 x 12 Continuous length
b) 500 FT	18 x 12 x 8 Continuous length
c) 100 FT	12 x 10 x 5 Continuous length
<i>[Spool dimensions may vary slightly]</i>	

www.alphawire.com

Alpha Wire | 711 Lidgerwood Avenue, Elizabeth, NJ 07207

Tel: 1-800-52 ALPHA (25742)

Although Alpha Wire ("Alpha") makes every reasonable effort to ensure there accuracy at the time of publication, information and specifications described herein are subject to errors or omissions and to changes without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary) whatsoever, even if Alpha had been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

RoHS CERTIFICATE OF COMPLIANCE

To Whom It May Concern:

Alpha Wire Part Number:6360

6360 , RoHS-Compliant Commencing With 3/1/2005 Production

*This document certifies that the Alpha part numbers cited above are manufactured in accordance with Directive 2002/95/EC of the European Parliament and of the Council of 27 January 2003, better known as the RoHS Directives, with regards to restrictions of the use of certain hazardous substances used in the manufacture of electrical and electronic equipment. The reader is referred to these Directives for the specific definitions and extents of these Directives. **No Exemptions are required for RoHS Compliance on this item.***

Substance	Maximum Control Value
Lead	0.1% by weight (1000 ppm)
Mercury	0.1% by weight (1000 ppm)
Cadmium	0.01% by weight (100 ppm)
Hexavalent Chromium	0.1% by weight (1000 ppm)
Polybrominated Biphenyls (PBB)	0.1% by weight (1000 ppm)
Polybrominated Diphenyl Ethers (PBDE)	0.1% by weight (1000 ppm)
Including Deca-BDE	0.1% by weight (1000 ppm)

The information provided in this document and disclosure is correct to the best of Alpha Wire's knowledge, information and belief at the date of its release. The information provided is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it will become part of. The intent of this document is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Authorized Signatory for the Alpha Wire Company:



Dave Watson, Director of Engineering & QA

11/1/2012