

Antenna - ANT-DIR-2459-01 - 2701186

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Panel antenna, 2.4 / 5 GHz, 9 dBi, linear vertical, N (female), IP67



Product Features

- ✓ For large distances with a line of sight

Key commercial data

Packing unit	0
Minimum order quantity	1
GTIN	 4 046356 717182
Custom tariff number	85177011
Country of origin	POLAND

Technical data

General data

Frequency range	2.4 GHz
Frequency range	2.4 GHz ... 2.5 GHz
Frequency range	5.15 GHz ... 5.875 GHz
Horizontal beamwidth	75 ° (At 2.4 GHz)
Vertical beamwidth	55 ° (At 2.4 GHz)
Impedance	50 Ω
Gain	9 dBi
Wind velocity	160 km/h (Has a force of 15 N)
Connection method	N (female)
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Width	80 mm
Height	101 mm
Length	35 mm
Material	

Antenna - ANT-DIR-2459-01 - 2701186

Classifications

ETIM

ETIM 3.0	EC001423
ETIM 4.0	EC000416
ETIM 5.0	EC000416

UNSPSC

UNSPSC 11	20142601
UNSPSC 12.01	20142601
UNSPSC 13.2	20142601
UNSPSC 6.01	20142601
UNSPSC 7.0901	20142601

eCl@ss

eCl@ss 4.0	27240409
eCl@ss 4.1	27240409
eCl@ss 5.0	27242215
eCl@ss 5.1	27242208
eCl@ss 6.0	27242208
eCl@ss 7.0	27242208