




FCI 3-Way APEX 2.8 mm Connection System



| INDEX TYPE | HOUSING COLOR | SEALED/ UNSEALED | FEMALE ASSEMBLY PART NUMBER | MALE ASSEMBLY PART NUMBER | TEMPERATURE RATING OF MATERIAL | WIRE INSULATION RANGE PER CAVITY (mm) |
|------------|---------------|------------------|-----------------------------|---------------------------|--------------------------------|---------------------------------------|
| A | DK GRN | SEALED | 54200346 | 54200354 | -40°C to +150°C | 1.70 – 2.77 |
| A | BLK | SEALED | 54200308 | 54200312 | -40°C to +125°C | 1.70 – 2.77 |
| A | BLK | UNSEALED | 54200300 | 54200304 | -40°C to +125°C | 1.50 – 4.09 |
| B | LT GREY | SEALED | 54200309 | 54200313 | -40°C to +125°C | 1.70 – 2.77 |
| B | LT GREY | UNSEALED | 54200301 | 54200305 | -40°C to +125°C | 1.50 – 4.09 |
| C | DK GREY | SEALED | 54200310 | 54200314 | -40°C to +125°C | 1.70 – 2.77 |
| D | NATURAL | SEALED | 54200311 | 54200315 | -40°C to +125°C | 1.70 – 2.77 |
| D | NATURAL | UNSEALED | 54200303 | 54200307 | -40°C to +125°C | 1.50 – 4.09 |
| C | DK GREY | UNSEALED | 54200302 | 54200306 | -40°C to +125°C | 1.50 – 4.09 |
| A | BLACK | SEALED | 54200335N* | — | SEAL W/O HOLES | USED AS CAP |
| A | BLACK | SEALED | — | 54200337* | SEAL W/O HOLES | USED AS CAP |

* Plug for same index (A) mating part.

Note: Female part numbers with the N suffix are without CPA latch.

3.35mm wire diameter sealing is available in select configurations. Consult sales drawing.

Additional configurations available. Please consult sales drawing.