


NOTES:

- 1.0 CAD MAINTAINED DRAWING. MANUAL CHANGES UNAUTHORIZED.
- 2.0 DIAMETER MEASURED USING VERNIERS.
- 3.0 STRIP SUPPLIED ON SPOOL IN CONTINUOUS LENGTH. 50 FT. MIN.
- 4.0 IDENTIFICATION: MARK EACH SPOOL WITH PART NO., QUANTITY, DATE CODE AND I.S. FED. IDENT. NO..

CREATED TABLE FOR CAT. PARTS	
ECD E64	
DCS 02/19/98	
EWS 02/20/98	05
ADDED -207 P/N	
TW 07/08/08	
	06

DWG NO. 8102-0000-XX



ITEM	"A" DIM	"B" DIM	"C" DIM
-0202	.130 <sup>+0.030</sup> / <sub>-0.000</sub>	.200 <sup>+0.030</sup> / <sub>-0.000</sub>	.125
-0203	.190 <sup>+0.030</sup> / <sub>-0.000</sub>	.250 <sup>+0.030</sup> / <sub>-0.000</sub>	.150
-0204	.250 <sup>+0.030</sup> / <sub>-0.000</sub>	.312 <sup>+0.040</sup> / <sub>-0.000</sub>	.187
-0205	.312 <sup>+0.040</sup> / <sub>-0.000</sub>	.380 <sup>+0.040</sup> / <sub>-0.000</sub>	.187
-0206	.375 <sup>+0.040</sup> / <sub>-0.000</sub>	.500 <sup>+0.050</sup> / <sub>-0.000</sub>	.250
-0207	.670 <sup>+0.060</sup> / <sub>-0.000</sub>	.750 <sup>+0.060</sup> / <sub>-0.000</sub>	.375

FINISHES	
ZINC, CLEAR CHROMATE	-49
CADMIUM, CLEAR CHROMATE	-48
SEMI-BRIGHT NICKEL	-47
SATIN TIN	-41
BRIGHT	-40
BRIGHT - NO TAPE	-00

	DRAWN BY	DATE	TOLERANCES NOT SHOWN		STANDARD ULTRAFLEX HOLLOW "D" SHAPE
	DCS	02/19/98	DECIMAL 2 PL'S	----	
	CHECKED BY	DATE	DECIMAL 3 PL'S	----	
	RKM	02/20/98	FRACTIONAL	±	
APPROVED BY	DATE	SCALE	N.T.S.	DWG NO.	8102-0000-XX
EWS	02/20/98			SUB	06